




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family JUMPER			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 1:1	title 1 x 2 LOW PROFILE JUMPER ASSEMBLY			
A	V31909	NRC	12/16/93	angles	linear					
B	V92896	DAI	09/20/99							
C	V20973	GIP	07/17/02	0°±2'						
D	M05-0205	ERE	09/29/05	dr	M. CORNMANN	12/16/93				
E	M06-0238	MN	06/17/06	enrg	L.FYE	12/16/93				
F	M06-0389	AGS	10/4/06	chr	L.FYE	12/16/93				
				appd	L.FYE	12/16/93				
sheet index	revision sheet	F 1	F 2							

PRODUCT NOTE 3	CONTACT PLATING	HSG COLOR
93987-102	15u"/.38u Au OVER 50u"/1.27u Ni	NATURAL
93987-202	30u"/.76u Au OVER 50u"/1.27u Ni	NATURAL
93987-302	100u"/2.54u Sn	NATURAL

NOTE 6

NOTES:

- ① MATERIAL: LCP UL-94-V0
2. RECOMMENDED APPLICATION DATA:
 - A. ALL MATING PINS TO BE .025/.64 SQ ON TRUE CENTERS OF GIVEN TERMINAL SPACING WITHIN .015/.38 DIA .
 - B. SUGGESTED MATING PIN LENGTH .160/4.06 MIN.
- ③. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ④. THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
- ⑥. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKERS GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

XXXXXX-XYLF

BASE NUMBER

LEAD FREE OPTION
No. OF POSITIONS
PLATING CODE

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕-△		product family JUMPER			
ltr	ecn	no	dr	date	tolerances unless otherwise specified				INCH/MM		title		
F					angles	linear	.XX±.01/.3			1 x 2 LOW PROFILE JUMPER ASSEMBLY			
					0°±2'		.XXX±.005/.13						
							.XXX±.0020/.051	scale 1:1					
					dr	M. CORNMAN	12/16/93	FCJ		dwg no			
					enr	L.FYE	12/16/93			sheet 2 of 2			
					chr	L.FYE	12/16/93			size			
					appd	L.FYE	12/16/93			A3			
sheet index		revision sheet											