



DASH NO.	DESCRIPTION	MADE FROM
----------	-------------	-----------



NOTES:

1. FOR USE WITH RG-142, 223 & 400/U CABLE GROUPS.
2. FOR CABLE TRIMMING USE KTT-113 & KTD-166.
3. FOR FORMING USE CRIMP DIE SIZE 01.
4. FOR CABLING INSTRUCTIONS SEE CP-965.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
3 PLACE DECIMALS $\pm .004$ ANGLES $\pm 0^\circ 30'$
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

8	1	CABLING INSTRUCTIONS	3-102-2M88
7	1	ENG CRIMP CAPTIVE CONTACT M	1-563-19M9D
6	1	INSULATOR	
5	1	COUPLING NUT	
4	1	GASKET	
3	1	C-RING	
2	1	K-GRIP BODY ASS'Y.	
1	1	K-GRIP SLEEVE	5-89-05-2-MC7
ITEM	REQ'D	DESCRIPTION	PART NO.

REVISIONS

ISSUE	CHANGES
0	ER 13606 LI 18 JUL 74
1	CN 13841 A M.J.B 11 OCT 74
2	CN 14475 C GA 13 MAY 75
3	CN 15977 A GA 15 JUL 76
4	CN 21657 C HELEN 23 FEB 81
7	CN 32301 A LNM 19 JUN 90

KA-59-292

USED ON:

REF:

FINISH

SPEC. KER 10004

MATL

SPEC.

TNC PLUG

DRAWN W.D.

DATE 2 MAY 74

APPR. LI

DATE 18 JUL 74

KINGS ELECTRONICS

40 MARLBOROUGH ROAD
TUCKAHOE, N. Y. 10707

M39012/26-0503

SD