

Specification Status: Released

Electrical Rating

Voltage: 16V_{DC} MAX

Insulating Material:

Cured, Flame Retardant Epoxy Polymer

Lead Material:

18 AWG Tin Plated Copper
 (1.0 mm [0.040] nom. diameter)

Part Marking:

— Manufacturer's Mark
 G14 and Part Identification
 — Lot Identification




TABLE I. INSTALLATION ENVELOPE DIMENSIONS:

mm: in*	A		B		C		D		E		F		G	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	TYP	MIN	MAX	
	--	23.5	--	28.7	9.4	10.9	7.6	--	--	3.5	1.4	--	7.82	
	--	(0.925)	--	(1.13)	(0.37)	(0.43)	(0.30)	--	--	(0.14)	(0.06)	--	(0.308)	

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

CURRENT RATINGS			TIME TO TRIP		INITIAL RESISTANCE		R ₁ MAX 1 HR. POST TRIP RESISTANCE STANDARD TRIP		R _A MAX		TRIPPED-STATE POWER DISSIPATION	
AMPS AT 25°C			SECONDS AT 25°C, 70 A MAX		OHMS AT 25°C		OHMS AT 25°C		OHMS AT 25°C		WATTS AT 25°C TYP	
HOLD AT R ₁ MAX	HOLD AT R _A MAX	TRIP			MIN	MAX						
14.0	13.0	27.3	9.0	0.0022	0.0043		0.0064		0.0067		4.6	

Reference Documents:

PS400, PS300 (reference for R₁ MAX)

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Halogen Free*

Directive 2002/95/EC
 Compliant

Directive 2000/53/EC
 Compliant



* Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.

PolySwitch®
PTC Devices
Overcurrent Protection Device

PRODUCT: AGRF1400

 DOCUMENT: SCD25240
 REV LETTER: E
 REV DATE: JANUARY 25, 2013
 PAGE NO.: 2 OF 2

TABLE III. AUTOMOTIVE SPECIFIC STRESS TESTS AND TEST CONDITIONS:

ELECTRICAL STRESS TESTS	TEST CONDITIONS (see note 2)
ESD Voltage Withstand (see note 1)	25kV
Short Circuit Fault Current Durability	25 cycles, 16V, 200A
Fault Current Durability	350 cycles, 16V/100A
End-of-life Mode Verification	1750 cycles, 16V/100A
Jump Start Endurance (see note 1)	3 cycles, 26V, 1 minute duration
Load Dump Endurance (see note 1)	10 cycles, 86.5V

Note 1: The PolySwitch devices are tested in series with a load resistance and the voltages specified in the test conditions are shared between the PolySwitch device and the load resistance as specified in PS400.

Note 2: Please refer to Appendix A of PS400 for the detailed test procedures