

view X
board layout

position 5 9 13 17 21 25 27 28 30 32 33

position 8 12 16 20 24 26 29 31 34

$\phi 1,75 \pm 0,05$

$\phi 2,49 \pm 0,05$

$\phi 1,6 \pm 0,09$ 2)


$\phi 1 \pm 0,09$ 1)

8x $\phi 0,1$ (M)

22x $\phi 0,1$ (M)

2x $\phi 0,1$ (M)

6,6 3,9 2,2 26,6 23,9 22,55 21,2 18,5 14,5 13,7 12 9,4 10 6 2 3 4,5 4,5 9,59



2) drill hole diameter: $\varnothing 1.75 \pm 0.025$ mm
2) through hole diameter (after plating): $\varnothing 1.6^{+0.09}$ mm

1) drill hole diameter: $\varnothing 1.15 \pm 0.025$ mm
1) through hole diameter (after plating): $\varnothing 1.0^{+0.09}$ mm

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2 : 1	AdvancedTCA backplane power connector 30-pole, press-fit	
			Detail.	19.09.07	HL.			
			Insp.	19.09.07	Ko			
36396	09.12.11	HL.	Stand.					
34811	17.06.08	HL.	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 16 31 030 1201 000	Blatt/ page /
33903								
Mod.	Dat.	Name						