




LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	OWN
CM	00	G1		REVISED PER ECO-08-019746	13AUG08	HMR
		G2		REV PER ECO-09-021826	08SEP09	KK



- 1 MATES WITH AMP CONNECTOR PART NO. 480708.
- 2 FLAME RETARDANT CLASSIFICATION OF MATERIAL IS 94V-2.
- 3 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- 4 CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN STRIPED WITH 0.00076 [0.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- 5 CONTACT IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN 0.00076 [0.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED LAYOUT FOR 3.18 [0.125] THICK PC BOARD

6	PH BRZ GOLD 5	NYLON,NATURAL 2	350991-5
	PH BRZ TIN	NYLON,NATURAL 2	350991-4
	PH BRZ GOLD 4	NYLON,NATURAL 2	350991-3
CONTACT		HOUSING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 11OCT2005	 Tyco Electronics Corporation Harriaburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 11OCT2005	NAME S. RIDGILL 11OCT2005 SOCKET HEADER ASSEMBLY, 12 CIRCUIT, LONG TAIL, UNIVERSAL MATE-N-LOK (TM)		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ±		APPLICATION SPEC			
1 PLC ±		SIZE			
2 PLC ±		CAGE CODE			
3 PLC ± 0.13 [0.005]		DRAWING NO			
4 PLC ±		RESTRICTED TO			
ANGLES		A1 00779 C=350991			
FINISH		CUSTOMER DRAWING			
MATERIAL		SCALE 5:1			
SEE TABLE		SHEET 1 OF 1			
		REV G2			

METRIC