



STRIP MATERIAL NUMBER	FINISH
84524-0012	OVERALL NICKEL 80µ" MINIMUM
84524-0018	SELECTIVE HARD GOLD 30µ" MINIMUM OVER NICKEL 50µ" MINIMUM



WIRE INSULATION O.D. RANGE $\frac{.095-.150}{2.41-3.81}$

- NOTES:
1. MATERIAL: COPPER ALLOY .0118/0.300 THICK.
 2. FINISH: SEE CHART.
 3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
 4. TERMINAL FOR USE ON XRC CONNECTOR ASSEMBLIES.
 5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.
 6. TERMINALS COMPLY WITH SECTION 5.3.2 OF THE SAE J1939-11 STANDARD FOR SURFACE VEHICLE RECOMMENDED PRACTICE.



ADD NOTE 6 & UPDATE OD EC NO: IPG2013-1752 DRAWN: WLEUNG 2013/06/06 CHKD: KJ02WIK 2013/06/07 APPR: JFUMPHY 2013/06/20		QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE XRC PIN TERMINAL 14-18AWG .095-.150" WIRE DIA. MOLEX MOLEX INCORPORATED				
			4 PLACES	± ---	± ---	MODELL	2009/04/15					
			3 PLACES	± ---	± .005	CHECKED BY	DATE	SHEET NO. 1 OF 1				
			2 PLACES	± .13	± ---	RDEROSS	2009/04/15					
1 PLACE	± ---	± ---	APPROVED BY	DATE								
			ANGULAR ± ---°		DTITUS	2010/10/13						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.					
					SEE CHART		SD-84524-003					
					SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						