




LOC		DIST		REVISIONS			
AA		00		REV	DESCRIPTION	DATE	OWN
				B	ECO-06-011837	20MAY2006	JW

1. MATERIAL: HOUSING - HIGH TEMPERATURE THERMOPLASTIC, SEE TABLE FOR COLOR.
TERMINALS - 0.3[.012] THICK COPPER ALLOY PLATED WITH 1.27 μ m[.000050] MINIMUM GOLD IN LOCALIZED CONTACT AREA, 2.5 μ m[.000100] MINIMUM MATTE TIN ON TERMINATION END, OVER 1.27 μ m[.000050] MINIMUM NICKEL OVER THE ENTIRE TERMINAL.
BOARDLOCK - BRASS, 1/2 HARD, 2.54 μ m[.000100] MINIMUM MATTE TIN OVER 1.27 μ m[.000050] MINIMUM NICKEL.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- 3 DATUM ESTABLISHED BY CUSTOMER.
- 4 PACKAGING TAPE AND REEL:(PER EIA 481 SPEC)
TAPE - 44mm[1.73] WIDE
POCKET PITCH - 24mm[.945]
CORRUGATED REEL DIAMETER - 560mm[22.0]
PIECES/REEL - 650
- 5 PACKAGING TAPE AND REEL:(PER EIA 481 SPEC)
TAPE - 44mm[1.73] WIDE
POCKET PITCH - 24mm[.945]
PLASTIC REEL DIAMETER - 330mm[13.0]
PIECES/REEL - 200
- 6 MANUFACTURING DATE CODE LOCATED APPROXIMATELY AS SHOWN. FIRST 2 DIGITS ARE YEAR, SECOND 2 DIGITS ARE WORK WEEK, AND LAST DIGIT IS DAY OF THE WEEK

MARKING		COLOR		PACKAGING		PART NUMBER	
NONE		GRAY		4		5406903-4	
6		GRAY		5		5406903-2	
		GRAY		4		5406903-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG J. ALCORTA - 15JUN2005 CHK J. WESTMAN 16JUN2005		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME S. FLICKINGER 16JUN2005 PRODUCT SPEC 108-1689 APPLICATION SPEC 114-6040	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		SIZE A1 CAGE CODE 00779 DRAWING NO 5406903 RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1	