



TYPICAL PASSBAND CHARACTERISTIC



DIMENSION



SPECIFICATION

Application	DECT				
	SYMBOL	Min	Typ.	Max.	Unit
Center Frequency	f_O		1890		MHz
Bandwidth	BW	$f_O \pm 10$			MHz
Insertion Loss	IL			1.5	dB
Ripple				0.5	dB
Standing Wave Ratio	VSWR			2.0	
Impedance	Z		50		Ω
Attenuation	1660~1680MHz	30			dB
	1770~1790MHz	10			
	3760~3800MHz	10			
	5640~5700MHz	10			