


MINIATURE RELAY

2 POLES—1 to 2 A (FOR SIGNAL SWITCHING)

A SERIES

■ FEATURES

- Extremely low profile and light weight
—Height: 5 mm
—Weight: approximately 1.2 g
- UL, CSA recognized
- Conforms to FCC rules and regulations part 68
—Surge strength 1,500 V
- High reliability—bifurcated contacts
- Wide operating range
- DIL pitch terminals
- Plastic sealed type
- Latching version available



■ ORDERING INFORMATION

[Example] $\frac{A}{(a)} \quad \frac{L}{(b)} - \frac{D}{(*)} \quad \frac{12}{(c)} \quad \frac{W}{(d)} - \frac{K}{(e)} \quad \frac{K}{(f)}$

(a)	Series Name	A : A Series
(b)	Operation Function	Nil : Standard type L : Latching type
(c)	Number of Coil	Nil : Single winding type D : Double winding type
(d)	Nominal Voltage	Refer to the COIL DATA CHART
(e)	Contact	W : Bifurcated type
(f)	Enclosure	K : Plastic sealed type

Note: Actual marking omits the hyphen (-) of (*)

■ SAFETY STANDARD AND FILE NUMBERS

UL478, 508 (File No. E45026)

C22.2 No. 14 (File No. LR35579)

Nominal voltage	Contact rating
1.5 to 48 VDC	0.5 A 125 VAC 2 A 30 VDC 0.3 A 110 VDC — resistive

Only UL/CSA approval markings are marked on the cover.

■ SPECIFICATIONS

Item			Standard Type	Single Winding Latching Type	Double Winding Latching Type
			A-() W-K	AL-() W-K	AL-D () W-K
Contact	Arrangement		2 form C (DPDT)		
	Material		Gold overlay silver alloy		
	Resistance (initial)		Maximum 50 mΩ (at 1 A 6 VDC)		
	Rating (resistive)		0.5 A 125 VAC or 1 A 30 VDC		
	Maximum Carrying Current		2 A		
	Maximum Switching Power		62.5 AV/30 W		
	Maximum Switching Voltage		250 VAC, 220 VDC		
	Maximum Switching Current		2 A		
	Minimum Switching Load*1		0.01 mA 10 mVDC		
	Capacitance		Approximately 0.5 pF (between open contacts, adjacent contacts) Approximately 1.0 pF (between coil and contacts)		
Coil	Nominal Power (at 20°C)		0.14 to 0.3 W	0.1 to 0.15 W	0.20 to 0.3 W
	Operate Power (at 20°C)		0.08 to 0.17 W	0.06 to 0.85 W	0.15 to 0.17 W
	Operating Temperature		−40°C to +85°C (no frost) (refer to the CHARACTERISTIC DATA)		
Time Value	Operate (at nominal voltage)		Maximum 6 ms	Maximum 6 ms (set)	
	Release (at nominal voltage)		Maximum 4 ms	Maximum 6 ms (reset)	
Insulation	Resistance (at 500 VDC)		Minimum 1,000 MΩ		
	Dielectric Strength	between open contacts	1,000 VAC 1 minute		
		between adjacent contacts	1,000 VAC 1 minute		
		between coil and contacts	1,000 VAC 1 minute		
	Surge Strength		1,500 V (between coil and contacts)		
Life	Mechanical		1 × 10 ⁸ operations minimum	1 × 10 ⁷ operations minimum	
	Electrical		2 × 10 ⁵ ops. min. (0.5 A 125 VAC), 5 × 10 ⁵ ops. min. (1 A 30 VDC)		
Other	Vibration Resistance	Misoperation	10 to 55 Hz (double amplitude of 3.3 mm)		
		Endurance	10 to 55 Hz (double amplitude of 5.0 mm)		
	Shock Resistance	Misoperation	500 m/s ² (11 ±1 ms)		
		Endurance	1,000 m/s ² (6 ±1 ms)		
	Weight		Approximately 1.2 g		

*1 Minimum switching loads mentioned above are reference values. Please perform the confirmation test with the actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ COIL DATA CHART

	MODEL	Nominal voltage	Coil resistance ($\pm 10\%$)	Must operate voltage* ¹	Must release voltage* ¹	Nominal power
Standard Type	A-1.5W-K	1.5 VDC	16.1 Ω	+1.05 VDC	+0.15 VDC	140 mW
	A- 3 W-K	3 VDC	64.3 Ω	+2.1 VDC	+0.3 VDC	140 mW
	A-4.5W-K	4.5 VDC	145 Ω	+3.15 VDC	+0.45 VDC	140 mW
	A- 5 W-K	5 VDC	178 Ω	+3.5 VDC	+0.5 VDC	140 mW
	A- 6 W-K	6 VDC	257 Ω	+4.2 VDC	+0.6 VDC	140 mW
	A- 9 W-K	9 VDC	579 Ω	+6.3 VDC	+0.9 VDC	140 mW
	A-12 W-K	12 VDC	1,028 Ω	+8.4 VDC	+1.2 VDC	140 mW
	A-18 W-K	18 VDC	1,620 Ω	+12.6 VDC	+1.8 VDC	200 mW
	A-24 W-K	24 VDC	2,880 Ω	+16.8 VDC	+2.4 VDC	200 mW
	A-48 W-K	48 VDC	7,680 Ω	+33.6 VDC	+4.8 VDC	300 mW










Note: *¹ Specified values are subject to pulse wave voltage.
All values in the table are measured at 20°C.

	MODEL	Nominal voltage	Coil resistance ($\pm 10\%$)	Set voltage* ¹	Reset voltage* ¹	Nominal power
Single Winding Latching Type	AL-1.5W-K	1.5 VDC	22.5 Ω	+1.05 VDC	-1.05 VDC	100 mW
	AL- 3 W-K	3 VDC	90 Ω	+2.1 VDC	-2.1 VDC	100 mW
	AL-4.5W-K	4.5 VDC	203 Ω	+3.15 VDC	-3.15 VDC	100 mW
	AL- 5 W-K	5 VDC	250 Ω	+3.5 VDC	-3.5 VDC	100 mW
	AL- 6 W-K	6 VDC	360 Ω	+4.2 VDC	-4.2 VDC	100 mW
	AL- 9 W-K	9 VDC	810 Ω	+6.3 VDC	-6.3 VDC	100 mW
	AL-12 W-K	12 VDC	1,440 Ω	+8.4 VDC	-8.4 VDC	100 mW
	AL-18 W-K	18 VDC	2,160 Ω	+12.6 VDC	-12.6 VDC	150 mW
	AL-24 W-K	24 VDC	3,840 Ω	+16.8 VDC	-16.8 VDC	150 mW
Double Winding Latching Type	AL-D1.5W-K	1.5 VDC	P 11.25 Ω	+1.05 VDC		200 mW
			S 11.25 Ω		+1.05 VDC	
	AL-D 3 W-K	3 VDC	P 45 Ω	+2.1 VDC		200 mW
			S 45 Ω		+2.1 VDC	
	AL-D4.5W-K	4.5 VDC	P 101 Ω	+3.15 VDC		200 mW
			S 101 Ω		+3.15 VDC	
	AL-D 5 W-K	5 VDC	P 125 Ω	+3.5 VDC		200 mW
			S 125 Ω		+3.5 VDC	
	AL-D 6 W-K	6 VDC	P 180 Ω	+4.2 VDC		200 mW
			S 180 Ω		+4.2 VDC	
	AL-D 9 W-K	9 VDC	P 405 Ω	+6.3 VDC		200 mW
			S 405 Ω		+6.3 VDC	
	AL-D12 W-K	12 VDC	P 720 Ω	+8.4 VDC		200 mW
			S 720 Ω		+8.4 VDC	
	AL-D18 W-K	18 VDC	P 1,080 Ω	+12.6 VDC		300 mW
			S 1,080 Ω		+12.6 VDC	
	AL-D24 W-K	24 VDC	P 1,920 Ω	+16.8 VDC		300 mW
			S 1,920 Ω		+16.8 VDC	




Note: *¹ Specified values are subject to pulse wave voltage.
All values in the table are measured at 20°C.

P: Primary coil S: Secondary coil











CHARACTERISTIC DATA



REFERENCE DATA




A SERIES




■ DIMENSIONS

● Dimensions


A, AL type (Non-latching type, single winding latching type)






● Schematics (Bottom View)



● PC board mounting hole layout (Bottom View)



AL-D type (Double winding latching type)



Unit: mm

Fujitsu Components International Headquarter Offices

Japan

Fujitsu Component Limited
Gotanda-Chuo Building
3-5, Higashigotanda 2-chome, Shinagawa-ku
Tokyo 141, Japan
Tel: (81-3) 5449-7010
Fax: (81-3) 5449-2626
Email: promothq@ft.ed.fujitsu.com
Web: www.fcl.fujitsu.com

North and South America

Fujitsu Components America, Inc.
250 E. Caribbean Drive
Sunnyvale, CA 94089 U.S.A.
Tel: (1-408) 745-4900
Fax: (1-408) 745-4970
Email: marcom@fcai.fujitsu.com
Web: www.fcai.fujitsu.com

Europe

Fujitsu Components Europe B.V.
Diamantlaan 25
2132 WV Hoofddorp
Netherlands
Tel: (31-23) 5560910
Fax: (31-23) 5560950
Email: info@fceu.fujitsu.com
Web: www.fceu.fujitsu.com

Asia Pacific

Fujitsu Components Asia Ltd.
102E Pasir Panjang Road
#04-01 Citilink Warehouse Complex
Singapore 118529
Tel: (65) 6375-8560
Fax: (65) 6273-3021
Email: fcal@fcal.fujitsu.com
www.fcal.fujitsu.com

© 2003 Fujitsu Components America, Inc. All company and product names are trademarks or registered trademarks of their respective owners. Rev. 02/12/2003