




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO	CLEARANCE HOLE FOR SCREW	HOLE DIA
MTM1H-C	#8 (4mm)	.176 (4.47mm)
MTM1H10-C	#10 (5mm)	.214 (5.43mm)
MTM1H25-C	#14 (6mm)	.281 (7.14mm)




NOTES:

1. DIMENSIONAL TOLERANCES:
 $.XX \pm .02 (.50)$
 $.XXX \pm .010 (.254)$
2. USE WITH STD, LIGHT HEAVY, HEAVY MLT'S & 3/8" STRAPPING.
3. DIM'S IN () ARE mm.
4. PACKAGE C = 100



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
07A	02/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW PANDUIT GLOBAL TITLE BLOCK WITH PANDUIT LOGO	SSECN01031
06A	09/04	JAMB	EJD	----	Ⓒ ADDED "LIGHT-HEAVY" MLT'S TO NOTE 2. Ⓓ CHANGED "AISI NO. 5 EDGE" TO "BROCKEN EDGES"	12052
05	06/04	JAMB	DPN	----	Ⓑ CHANGED PART NO. MTM1H8-C TO MTM1H-C	11723
04	05/04	JAMB	DPN	----	Ⓐ PART NO.CHANGED FROM MTM1H14C TO MTM1H25C	11714
03	05/02	JAMB	DPN	----	MATERIAL WAS 302 S.S.	10042
02	01/01	KMD	JAC	----	ADDED NOTE 4. CAD FILE SPEC WAS NPC-S41042_01	09010
01	5/92	DL	LM	----	ADDED MTM1H10 & MTM1H14	01012

TITLE				
METAL TIE MOUNT (1) HOLE				
CUSTOMER DRAWING				
ITEM REVISION NAME		N41042BS/07		
DATASET FILE NAME		N41042BS_DC/07A		
		MATERIAL:		
		304 STAINLESS STEEL		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:		
$.x \pm .1 [2.54]$		N41042BS_DC		
$.xx \pm .01 [.25]$		THIRD ANGLE PROJECTION		
$.xxx \pm .005 [.127]$		SCALE		
ANGLES $\pm 5^\circ$		SHT 1 OF 1		
DRAWN BY		DATE		SIZE
SAM		3/25/91		A
CHK		JAC		
		2:1		