

THIS DRAWING IS UNPUBLISHED
VERTRÄULICHE UNVERÖFFENTLICHE ZEICHNUNG

© COPYRIGHT 2000

RELEASE FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

BY AMP INCORPORATED

2000

ALL RIGHTS RESERVED
ALLE RECHTE VORBEHALTEN

MATED WITH:
PASSEND ZU:

1103149

1

2

3

4

LOC

DIST

REVISIONS
ÄNDERUNGEN

AI

-

P

LTR

DESCRIPTION
BESCHREIBUNG

DATE

DWN

APVD

PROJEKT NR.
EGGMN04419

D1

RELEASED AS PER ECR-07-021780

9/14/2007

PB

TS

CONTACT ARRANGEMENT
VIEW FROM TERMINATION SIDE

CONTACT ARRANGEMENT
VIEW FROM CONNECTING SIDE

CONTACT ARRANGEMENT
VIEW FROM TERMINATION SIDE

Panel cut-out for contact insert
when used without housing

0-1103148-1
HMX.4/8.Sti.S
16A/380V 6 KV 3
80A/380V 6 KV 3

10

9

5

8

1

7

6

4

3

2

(1 : 1)

A (3 : 1)

* distance for guaranteed
contact 21 mm max.

NOTES

1 POWER CONTACT: 1 TO 4
OUTER DIMENSIONS OF INSULATION: MAX. Ø10,3 MM

2 SIGNAL CONTACT: 5 TO 12
OUTER DIMENSIONS OF INSULATION: MAX. Ø5,2 MM

3 GROUNDING CONTACT

4 SUITABLE HOOD SIZE 8: SERIES HB; HD; EMV AND HIP

5 STANDARDS:
DIN EN 61984; DIN EN 60664-1

6 PACKAGING:
5 PIECES IN A CARTON

0-1 AS SHOWN
ORDERING TEXT: HMX.4/8.Sti.S

8 SIGNAL WIRE PROTECTION STRIP

4 THREADED PIN

8 CONTACT SCREW WITH SLOT

1 CLAMP TAB

1 CYLINDER SCREW , M5

4 FIXING SCREW

2 GROUNDING CONTACT-PIN

8 PIN CONTACT (SIGNAL)

4 PIN CONTACT (POWER)

1 MALE INSERT HMX.4.8

QTY

DESCRIPTION

MATERIAL

SURFACE

COLOR

NOTE

ITEM

10

9

8

7

6

5

4

3

2

1

0-1 HMX.4/8.Sti.S

12/22/2005

R.SRINIVAS

12/22/2005

M.SCHWEIGER

12/22/2005

T.SCHNURPFIL

108-74065

114-74067

1103148

1

1

1

D1

1103148

1

1

1

D1

HYPERMILL/EGGMN04419 Comp. H4903 Internal Models with IN-LINE_20070804

AMP 1471-9 REV 27JUN96 This is a TRANSLATED file from Computervision, Inc., Medusa Revision 12.2.5T