


©1968 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

Unpublished copy not to be reproduced without written permission of AMP Incorporated.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	O	NPS 6T-0579 (REV 3)	7-1-68	RHW
	A	REV TITLE PER ECN PC-5545	12-6-68	RHW
	B	REMOVED ENGINEERING CONT. P-6288 REVISED P-6293	4-17-70	FCY
	C	REVISED PER ECN P-6489	3-18-71	FCY
	D	REV PER G-5318	10/25/87	WJV



I	WIRE SPLICE	51942	INSERT: BRASS (MIL-C-50) TIN PL (MIL-T-10727) .0003 MIN EXT THK
			SPLICE: COPPER (QQ-C576) TIN PL (MIL-T-10727)
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .008$ ANGLES $\pm 5^\circ$			AMP INCORPORATED HARRISBURG, PENNSYLVANIA
CONTRACT NO. —#— DR <i>P. J. H. H. H.</i> 6-27-68 CHK <i>R. J. H. H.</i> 7-1-68 MATERIAL SEE TABLE APPD <i>Swabell</i> 7-2-69 DSGN APPD OTHER APPD			NAME WIRE SPLICE COPALUM-STRANDED/SOLID WIRE SIZE: 4 TO 6
AMP INFO LOC <i>G-86</i> PRINT DATE <i>7-2-69</i> HEAT TREAT <i>H</i> FINISH SEE TABLE			SIZE B CODE IDENT NO. 00779 NUMBER 51942
SCALE 2:1			WT CALC ACTUAL SHEET 1 OF 1