

SPECIFICATION FOR APPROVAL

TO : _____

REF. No. _____

APPROVED DATE 	CHECKED DATE  	PREPARED DATE 
---	---	---

MODEL No. AP0512MX-GB0 P.S. (8)A80G

DESCRIPTION: DC FAN (Lead Free) REV. A

ID No. _____

THIS OFFER IS MADE ACCORDING TO YOUR CURRENT INQUIRY.
UNLESS OTHERWISE REVISED, THIS SPECIFICATION WILL BE FINAL FOR
ALL FUTURE PRODUCTION OF ORDERS FROM YOUR RESPECTED COMPANY

KINDLY STUDY IN DETAILS AND RETURN TO US THE DUPLICATE
SIGNED AS YOUR CONFIRMATION OF SAME.



ADDA CORP.
REGISTERED TO ISO 9001
ISO/TS 16949
CERTIFICATE NO. A8035

ADDA **ADDA CORPORATION**

DATA - SHEET

Engineering

BRUSHLESS AXIAL COOLING FANS.

Printed on: 07/10/23

Customer :		Ref: (RoHS)																																			
ADDA Model No. : AP0512MX-GB0		P.S:(8)A80G																																			
Samples attached : piece(s)																																					
Safety Approval : CE																																					
<u>Specifications</u> <table border="1"> <thead> <tr> <th>ITEM</th> <th>SPECIFICATION / CONDITION</th> </tr> </thead> <tbody> <tr> <td>DIMENSIONS</td> <td>: 50x50x10 MM</td> </tr> <tr> <td>BEARING TYPE</td> <td>: HYPRO</td> </tr> <tr> <td>RATED VOLTAGE</td> <td>: 12.0 VDC</td> </tr> <tr> <td>OPERATING VOLTAGE RANGE</td> <td>: 10.8 VDC - 13.2 VDC</td> </tr> <tr> <td>START-UP VOLTAGE</td> <td>: 9.0 VDC, NOMINAL</td> </tr> <tr> <td>RATED CURRENT</td> <td>: 0.100 Amp. + 10% MAX</td> </tr> <tr> <td>RATED POWER</td> <td>: 1.20 Watt.</td> </tr> <tr> <td>RATED SPEED</td> <td>: 4000 RPM $\pm$ 10% (IN FREE AIR AT RATED VOLTAGE)</td> </tr> <tr> <td>AIR FLOW</td> <td>: 7.8 CFM (IN FREE AIR AT RATED VOLTAGE)</td> </tr> <tr> <td>STATIC AIR PRESSURE</td> <td>: 0.055 Inch Water (IN FREE AIR AT RATED VOLTAGE)</td> </tr> <tr> <td>NOISE LEVEL</td> <td>: 21.6 dB/A</td> </tr> <tr> <td>MOTOR PROTECTION</td> <td>: BY IMPEDANCE</td> </tr> <tr> <td>CONNECTION LEAD TYPE</td> <td>: WIRE ,AWG#28</td> </tr> <tr> <td>LIFE EXPECTANCY</td> <td>: 50000 Hours at 25°C / 65%</td> </tr> <tr> <td>NET WEIGHT</td> <td>: 9 Gram.</td> </tr> <tr> <td>PACKING</td> <td>: 108 pcs. per Export Carton</td> </tr> </tbody> </table> Unless otherwise stated, the relative humidity is 65%, and the temperature is 25°C for the standard testing. Should you have any doubt, please refer to the environmental conditions specified in the acknowledgement document.				ITEM	SPECIFICATION / CONDITION	DIMENSIONS	: 50x50x10 MM	BEARING TYPE	: HYPRO	RATED VOLTAGE	: 12.0 VDC	OPERATING VOLTAGE RANGE	: 10.8 VDC - 13.2 VDC	START-UP VOLTAGE	: 9.0 VDC, NOMINAL	RATED CURRENT	: 0.100 Amp. + 10% MAX	RATED POWER	: 1.20 Watt.	RATED SPEED	: 4000 RPM $\pm$ 10% (IN FREE AIR AT RATED VOLTAGE)	AIR FLOW	: 7.8 CFM (IN FREE AIR AT RATED VOLTAGE)	STATIC AIR PRESSURE	: 0.055 Inch Water (IN FREE AIR AT RATED VOLTAGE)	NOISE LEVEL	: 21.6 dB/A	MOTOR PROTECTION	: BY IMPEDANCE	CONNECTION LEAD TYPE	: WIRE ,AWG#28	LIFE EXPECTANCY	: 50000 Hours at 25°C / 65%	NET WEIGHT	: 9 Gram.	PACKING	: 108 pcs. per Export Carton
ITEM	SPECIFICATION / CONDITION																																				
DIMENSIONS	: 50x50x10 MM																																				
BEARING TYPE	: HYPRO																																				
RATED VOLTAGE	: 12.0 VDC																																				
OPERATING VOLTAGE RANGE	: 10.8 VDC - 13.2 VDC																																				
START-UP VOLTAGE	: 9.0 VDC, NOMINAL																																				
RATED CURRENT	: 0.100 Amp. + 10% MAX																																				
RATED POWER	: 1.20 Watt.																																				
RATED SPEED	: 4000 RPM $\pm$ 10% (IN FREE AIR AT RATED VOLTAGE)																																				
AIR FLOW	: 7.8 CFM (IN FREE AIR AT RATED VOLTAGE)																																				
STATIC AIR PRESSURE	: 0.055 Inch Water (IN FREE AIR AT RATED VOLTAGE)																																				
NOISE LEVEL	: 21.6 dB/A																																				
MOTOR PROTECTION	: BY IMPEDANCE																																				
CONNECTION LEAD TYPE	: WIRE ,AWG#28																																				
LIFE EXPECTANCY	: 50000 Hours at 25°C / 65%																																				
NET WEIGHT	: 9 Gram.																																				
PACKING	: 108 pcs. per Export Carton																																				
ADDA CORPORATION	Model No.: AP0512MX-GB0	P.S:(8)A80G	Page 1/4																																		



SPECIFICATION

1.0 SCOPE

- 1.1 If the information or other related document is inconsistent with this acknowledgement document, please refer to the acknowledge document.
- 1.2 This documentation defines the mechanical & electrical characteristics of DC brushless fans.
- 1.3 The specification of this product is described in details in the acknowledgement document. No guarantee is given to our product under the use of over specifications.
- 1.4 For any change or amendment to the specifications, such change will be noticed in writing beforehand.
- 1.5 If the product is used on the MIS system, please specify the specification in the purchase order.

2.0 MATERIAL

- 2.1 Frame : Aluminum alloy
- 2.2 Fan Blade : UL94V-0 Glass Filled polyester (P.B.T)
- 2.3 Bearing Sys. : ☐ Sleeve, oil impregnated.
☐ Two Ball Bearing
☐ One Ball one Sleeve
☒ Hypro Bearing
☐ FDB Bearing
- 2.4 RoHS : ☒ YES


3.0 DIMENSIONS & CONSTRUCTION

All dimensions, Direction of rotation and air flow were specified as per drawing attached.

4.0 CHARACTERISTICS & DEFINITION

- 4.1 All rated characteristics were specified as per data sheet enclosed.
- 4.2 Rated Current : Rated Current shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4.3 Rated Speed : Rated Speed shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4.4 Start Voltage : The voltage which is able to start the fan to operate by suddenly switching 'ON'.
- 4.5 Input Power : Input Power shall be measured after 3 minutes of continuous rotation at rated voltage.
- 4.6 Locked Rotor Current : Locked current shall be measured within one minute of rotor locked, after 3 minutes of continuous rotation at rated voltage in clean air.
- 4.7 Air Flow & Static Pressure : The air flow data and static pressures should be determined in accordance with AMCA standard or DIN24163 specification in a doublechamber testing with intake - side measurement.
- 4.8 Noise Level : The measurement of noise level is carried out with reference to CNS8753 in an anechoic chamber with the microphone positioned 1 meter from the air intake. Testing fan shall be hung in clean air.

NOISE LEVEL MEASUREMENT



SPECIFICATION

5.0 MECHANICAL INSPECTION

5.1 Rotation Direction

Counterclockwise when look into impeller side.

5.2 Protection

All fans have integrated protection against locked rotor condition so that there will be no damage to winding or any electronic component.

Restarting is automatic as soon as any constraint to rotation has been released.

As fan placed at dead angle position, and the switch was changed from off to on. Restarting was automatic normal as soon as and proved that this fan is good fan.

5.3 Locked Rotor Protection

No damage shall be found after 72 hours continuously at condition of rotation locked.

Restarting is automatic as soon as constraint to running has been released.

5.4 Avoid the damage, check the correct voltage and proper polarity before connecting with power.

5.5 Free Drop Shock

In minimum package condition, the fan should withstand drops on any three faces from a height of 30cm onto a wood board of 10mm thick.

5.6 Please do not stick a grease and/or an oil to the fan housing or blade which may have a harmful influence by a chemical reaction at high humidity.

5.7 If the fan is reinstalled, please pay special attention to the noise due to the vibration (or resonance).

5.8 During the testing of the fan, please make sure the finger guard is used for safety.

6.0 ELECTRICAL INSPECTION

6.1 Insulation Resistance

Not less than 10M ohm between housing and positive end of lead wire (red) at 500V DC.

6.2 Dielectric Strength

No damage should be found at 500 VAC for 60 seconds, measured with 1mA trip current between housing and positive end of lead wire.

6.3 Life Expectancy

The continuous duty life at given temperature after which, 90% of testing units shall still be running.

6.4 While the fan is running, do not intentionally lock the fan for a long time since the overheating of the motor produced by the long-time locking will damage the fan.

7.0 ENVIRONMENTAL

7.1 Improper use such as disassembling the fan, being covered with dust, or dipping the fan in water that results in defects is not covered in the warranty. Do not use the fan in the environment with corrosive air or liquid.

7.2 Operating Temperature / Humidity

-10°C to +70°C at humidity 65%+/-20% RH.

7.3 Storage Temperature

All function shall be normal after 500 hours storage at -40°C to +70 °C with a 24 hour recovery period at room temperature.

7.4 Humidity

After 96 hours, 95% RH, 40+/-2°C per MIL-STD-202F, method 103B humidity test, the measured data on insulation resistance and dielectric strength shall meet the specification.

7.5 Do not place or store the fan in the environment with high/low temperature/humidity. Do not store the fan for over 6 months; even if the fan is stored in room temperature for over 6 months, the fan may have the electric current leakage.



8.0 REMARKS

8.1 Material and construction are subject to change without advance notice. The changes should be within specification.

8.2 All fans shall meet the quality inspection under sampling plan MIL-STD-105E as follow:

Critical	0.25%
Major	1.00%
Minor	2.50%

9.0 OUTLINE STYLING & DIMENSIONS

The technical drawing illustrates the dimensions of the AP0512MX-GB0 fan. The front view shows a circular fan blade with a diameter of 43 mm. The lead wires are 135 ± 0.0 mm long. The fan is mounted on a base with a diameter of 61.6 ± 0.5 mm. The base has a central hole with a diameter of 20.0 ± 0.3 mm. The fan is secured with two screws, each with a diameter of 2.0 ± 0.1 mm. The side view shows the fan's thickness of 11 ± 0.5 mm. The top view shows the fan's footprint with a central square area of 25.8 mm by 25.8 mm, which is the location of the 25x25 mm PAD. The fan is secured with two screws, each with a diameter of 2.0 ± 0.1 mm. The base has a central hole with a diameter of 20.0 ± 0.3 mm. The fan is secured with two screws, each with a diameter of 2.0 ± 0.1 mm.

LEAD WIRES : UL 1571, AWG28 , L = 135 +/- 10 MM

Red = positive ; Black = negative.

10.0 Notes:

10.1 Please do not touch and push Fan Blade with fingers or others, fan blade and hypro bearings may be damaged and it causes noise defect.

10.2 Do not carry the fan by its lead wires.

10.3 If the fan does not have the polarity protection function, the connection of the colored wires should be red + red, and black + black, or else the fan will be damaged in no time.

10.4 For the models without reverse connection of polarity protection please do not connect the lead wire in reverse

A circular stamp with the date "2007.10.23" and a signature in Chinese characters.

ADDA CORPORATION

Model No. : AP0512MX-GB0 P.S:(8)A80G

Page 4 / 4

Page 4 / 4