




Clamping holder with positiv stop
M36x1,5 x 60,0

BES 30,0-KH-9LT



closed



opened

Application

The clamping holder with positive stop is used for holding proximity switches with M30 housings and mounting lengths 57 mm and longer. The plastic stop cap allows sensors with extended switching distance to be used with no change in the switching distance.

Characteristics

Housing material	CuZn
Union nut material	CuZn
Finish	white bronze plated
Positiv stop material	LCP with PTFE
Mounting thread	M 36x1,5
Mounting lenght	32,0 mm
Mounting type	Toggle clamp
Tightening torque max.	30 Nm
Temperature range	-25...+70 °C
Clamping cycles	20
Additional attributes	-

Definitions see general catalog

If not otherwise noted, ratings according to
DIN ISO 2768-mH