

**General ordering data**

Order No.	1792590000
Part designation	IPE 1.5N/3AN
Version	Earth terminal, 1.5 mm ² , Insulation displacement connection, Wemid, green, TS 35
EAN	4032248281602
Qty.	100 pc(s).

Product notes

Note, technical data	Conductor < 0.5 mm ² / AWG 24 with IRH 1.5
----------------------	---

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA02ATEX2241U
Download, German	KEMA02ATEX2241U_d.pdf
Download English	KEMA02ATEX2241U_e.pdf
ATEX conductor cross-section	1.5 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEX-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	green
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	3
Open sides	right

Additional technical data

Operating temperature range	- 50 °C, + 120 °C
Product family	I-Series
Type of connection	Insulation displacement connection
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	PE terminal

CSA rating data

Voltage (CSA)	300 V
Min. cross-section (CSA)	AWG 24
Max. cross-section (CSA)	AWG 16

Conductors for clamping (rated connection)

Clamping range, min.	0.21 mm²
Clamping range, max.	1.5 mm²
Type of connection	Insulation displacement connection
Connection direction	top
No. of connections	1
Blade size	0.6 x 3.5 mm
Solid, min.	0.21 mm²
Solid, max.	1.5 mm²
Flexible, min.	0.21 mm²
Flexible, max.	1.5 mm²
Flexible, min.	0.25 mm²
Flexible, max.	0.34 mm²
AWG conductor size, min.	0.25 mm²
AWG conductor size, max.	1.5 mm²

Dimensions

Width	5.1 mm
Height of lowest version	40.5 mm
Length	78.5 mm
TS 35 offset	33.5 mm

Mounting rail

Installation advice	TS 35
Length	78.5 mm
Material	Wemid
Standards	IEC 60947-7-2 / IEC 60352-4

PE rating data

PEN function	No
Pollution severity	3
Rated cross-section	1.5 mm²
Rated impulse withstand voltage to adjacent terminal	6 kV
Rated voltage for adjacent terminal	500 V
Standards	IEC 60947-7-2 / IEC 60352-4

UL rating data

Voltage (UL)	300 V
--------------	-------

UL rating data

Min. cross-section (UL)	AWG 24
Max. cross-section (UL)	AWG 16

Approvals

Approvals institutes

**Downloads**

STEP	1792590000_32827_IPE_1.5N-3AN_STP.stp
------	---------------------------------------

Classifications

ETIM 2.0	EC000901
ETIM 3.0	EC000901
eClass 4.1	27-14-03-05
eClass 5.0	27-14-03-05
eClass 5.1	27-14-03-05

Similar products

Order No.	Part designation	Version
1792560000	IPE 1.5N	Earth terminal, 1.5 mm ² , Insulation displacement connection, Wemid, green/yellow, TS 35
1792620000	IPE 1.5N/4AN	Earth terminal, 1.5 mm ² , Insulation displacement connection, Wemid, green/yellow, TS 35