



Features

- Lead free as standard
- RoHS compliant*
- Leadless
- High speed



CD1206-S0180 & S0180R are currently available, although not recommended for new designs. CD1206-S01575, CD1005-S0180 and CD1005-S0180R are preferred.

Switching Chip Diode Series - 1206

General Information

The markets of portable communications, computing and video equipment are challenging the semiconductor industry to develop increasingly smaller electronic components.

Bourns offers small-signal high-speed Switching Diodes for switching digital signal applications, in compact chip package 1206 size format, which offers PCB real estate savings and are considerably smaller than competitive parts. The Switching Diodes offer a forward current of 100 mA, a reverse voltage of 80 V and also have a low leakage reverse current option. The diodes are lead-free with Cu/Ni/Au plated terminations and are compatible with lead-free manufacturing processes, conforming to many industry and government regulations on lead-free components.

Bourns® Chip Diodes conform to JEDEC standards, are easy to handle on standard pick and place equipment and their flat configuration minimizes roll away.

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	CD1206-S0180	CD1206-S0180R	Unit
Forward Voltage (Max.)	V_F	1.00 ($I_f = 100\text{ mA}$)	1.00 ($I_f = 100\text{ mA}$)	V
Capacitance Between Terminals (Max.)	C_T	3 ($f = 100\text{ MHz}$, $V_r = 1\text{ V DC}$)		pF
Reverse Recovery Time (Max.)	t_{rr}	4 ($V_r = 6\text{ V}$, $I_f = 10\text{ mA}$, $R_L = 50\ \Omega$)		nS
Reverse Current (Max.)	I_R	0.1 ($V_r = 80\text{ V}$)	0.05 ($V_r = 75\text{ V}$)	μA

Absolute Ratings (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

Parameter	Symbol	CD1206-S0180	CD1206-S0180R	Unit
Repetitive Peak Reverse Voltage	V_{RRM}	90	90	V
Reverse Voltage	V_R	80	80	V
Average Forward Current	I_o	100	100	mA
Forward Current, Surge Peak	I_{surge}	1*	1*	A
Power Dissipation	PD	300	300	mW
Storage Temperature	T_{STG}	-55 to +125		$^\circ\text{C}$
Junction Temperature	T_J	-55 to +125		$^\circ\text{C}$

* Condition: 8.3 ms single half sine-wave superimposed on rate load (JEDEC method).

How To Order


CD 1206 - S 01 80 R

Common Code	_____				
Chip Diode	_____				
Package	_____				
• 1206					
Model	_____				
S = High Speed Switching					
Average Forward Current (I_o) Code	_____				
01 = 100 mA					
(Code x 1000 mA = Average Forward Current)					
Reverse Voltage (V_R) Code	_____				
80 = 80 V					
Reverse Current Suffix	_____				
R = Low Leakage I_R (CD1206-S0180R)					

Switching Chip Diode Series - 1206

BOURNS®


Product Dimensions



Dimension	1206
A	$\frac{3.00 - 3.20}{(0.118 - 0.126)}$
B	$\frac{1.40 - 1.60}{(0.055 - 0.063)}$
C	$\frac{0.50}{(0.020)}$ Typ.
D	$\frac{0.25}{(0.010)}$ R Typ.
E	$\frac{0.90 - 1.10}{(0.035 - 0.043)}$

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Recommended Pad Layout



Dimension	1206
A (Max.)	$\frac{3.00}{(0.118)}$
B (Min.)	$\frac{1.60}{(0.063)}$
C (Min.)	$\frac{1.40}{(0.055)}$

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

Physical Specifications

Case1206 (3216) Molded plastic
 TerminalsSolder plated, solderable per MIL-STD-750,
 Method 2026
 PolarityIndicated by cathode band
 Mounting PositionAny

Typical Part Marking


CD1206-S0180S1
 CD1206-S0180RS2

Switching Chip Diode Series - 1206


BOURNS®

Rating and Characteristic Curves: CD1206-S0180


Forward Characteristics




Reverse Characteristics



Derating Curve



Capacitance Between Terminals




Switching Chip Diode Series - 1206


BOURNS®

Rating and Characteristic Curves: CD1206-S0180R


Forward Characteristics




Reverse Characteristics



Derating Curve



Capacitance Between Terminals




Switching Chip Diode Series - 1206

BOURNS®

Packaging Information

The product will be dispensed in Tape and Reel format (see diagram below).



Item	Symbol	1206
Carrier Width	A	1.70 ± 0.10 (0.067 - 0.004)
Carrier Length	B	3.40 ± 0.10 (0.134 - 0.004)
Carrier Depth	C	1.25 ± 0.10 (0.049 - 0.004)
Sprocket Hole	d	1.55 ± 0.10 (0.061 - 0.004)
Reel Outside Diameter	D	178 (7.008)
Reel Inner Diameter	D ₁	60.0 (2.362) MIN.
Feed Hole Diameter	D ₂	13.0 ± 0.20 (0.512 - 0.008)
Sprocket Hole Position	E	1.75 ± 0.10 (0.069 - 0.004)
Punch Hole Position	F	3.50 ± 0.05 (0.138 - 0.002)
Punch Hole Pitch	P	4.00 ± 0.10 (0.157 - 0.004)
Sprocket Hole Pitch	P ₀	4.00 ± 0.10 (0.157 - 0.004)
Embossment Center	P ₁	2.00 ± 0.05 (0.079 - 0.002)
Overall Tape Thickness	T	0.20 ± 0.05 (0.008 - 0.002)
Tape Width	W	8.00 ± 0.20 (0.315 - 0.008)
Reel Width	W ₁	13.5 (0.531) MAX.
Quantity per Reel	--	3,000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[CD1206-S0180R](#) [CD1206-S0180](#)