

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-013423	13JUN06	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

Ni PLATING
- 5

THIS ITEM MUST BE WHITE
- 6

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 2 GHz

NOMINAL IMPEDANCE:75 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:1.50 mOhm Max

CENTRE CONTACT:0.20 mOhm Max

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 7

MECHANICAL CHARATERISTICS

COUPLING RETENTION FORCE:N/A

CABLE RETENETION FORCE:N/A


DURABILITY:500 Cycles Min
- 8

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC
- 9

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 10

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



		2	2	PTFE	INSULATION	12
		1	1	BRASS	SLEEVE	11
		1	1	BRASS	CONTACT II	10
		1	1	BRASS	WASHER	9
		1	1	SPRING STEEL	SPRING	8
		1	1	BRASS	RETAINING RING	7
		1	1	SILICON RUBBER	GASKET	6
		1	1	PTFE	INSULATION	5
		1	1	BRASS	BODY 2	4
		1	1	BRASS	SHELL	3
		1	1	BRASS	CONTACT I	2
		1	1	BRASS	BODY 1	1
		6--0	1--0	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY				PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

SEE TABLE

DWN J.SANDWELL 13JUN06

CHK S.PARLOW 13JUN06

APVD F.WHEELER-KING 13JUN06

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Bideford EX39 4HE

NAME
BNC TEE ADAPTOR J-P-J 75 OHM

SIZE A3

CAGE CODE 00779

DRAWING NO C-1478039

RESTRICTED TO -

SCALE NTS

SHEET 1 OF 1

REV B