





SECT. Z-Z



SECT. Y-Y

注記
NOTES

- 適合ハウジング: 51047シリーズ
APPLICABLE HOUSING: 51047 SERIES
- メッキ仕様 PLATING
錫 0.9μm MIN. リフロー処理 (前メッキ)
TIN 0.9μm MIN. REFLOW TREATMENT (PRE-PLATED)

角度	ANGLE	±3°
30°以上	OVER	±0.3
10°以上 30°未満	OVER UNDER	±0.25
10°未満	UNDER	±0.2
一般公差		
GENERAL TOLERANCES		

記号	変更内容	DR.	日付
LTR	REVISION RECORD	CHK.	DATE
D	変更 REVISED	H.H.	'93/9/3
C	変更&再作図 REVISED & REDRAWN	H.H.	'92/10/27
J30883		M.F.	
J20810		M.F.	

材料	リン青銅
MATERIAL	PHOSPHOR BRONZE
	(t=0.15)
仕上げ	—H—
FINISH	
適用電線範囲	AWG #26-28
WIRE RANGE	
被覆外径	0.5-1.0
INS. RANGE	
DRAWN BY	'92/10/27
H.HIRAMOTO	
CHK'D BY	'93/9/3
M.FUKUSHIMA	
APP'D BY	'93/9/3
M.FUKUSHIMA	
尺度	20 - 1
SCALE	

50125-8100	バラ状 LOOSE
50125-8000	連鎖状 CHAIN
ENG. NO.	端子形状 FORM

molex	MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社
REVISE ONLY ON CAD SYSTEM	
TITLE 名称	
1.25 WIRE TO WIRE CONN. CRIMP PLUG TERMINAL	

DWG. NO.	REV
SD-50125-8*00	D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[50125-8000](#) [50125-8000 \(Cut Strip\)](#) [50125-8000 \(Mouser Reel\)](#)