


D: OPTION GUIDE:

PART NO.	ITEM	TERMINAL DIFFERENCE
745W-XX/PP	1+2	Solder Terminal 2.8X0.8 mm
745W-XX/QQ	1+3	Solder Terminal 4.0X0.8 mm
745W-XX/RR	1+4	Quick Con. Terminal 4.8X0.8mm
745W-XX/SS	1+5	Quick Con. Terminal 6.3X0.8mm
"XX" Panel Thickness (A) in 1/10 mm		
PP: 01,05,09,13,17 QQ:02,06,10,14,18		
RR: 03,07,11,15,19 QQ:04,08,12,16,20		
745W-15/05:Panel thickness 1.5mm terminal 2.8mm		



Technical drawing showing two views of a mechanical component. The left view is a side elevation with a width dimension of 1.22 (31.0) and a height dimension of 1.29 (32.7). The right view is a front elevation with a height dimension of 0.12 (3.0) and a width dimension of 0.87 (22.0). A callout circle labeled '1' points to a feature on the right view. The right view also shows a dimension of 'A' + 0.2.

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number: 745W SERIES		
0-1	0.15	Description: AC RECEPTACLES		
1-6	0.20			
6-18	0.30			
18-50	0.50			
50-120	0.70	Drawn/Date K.Huang 11-21-98	Checked/Date 11-21-98	Approved/Date JJH/11-21-98
120-250	0.90			
250-500	1.20			