


Bipolar Power Transistors



Plastic (Isolated TO-220 Type)
Pin: 1 — Base, 2 — Collector, 3 — Emitter (Style 2, Case 221D-02)

Mfr.'s Type		I _c Cont (A) Max.	V _{CEO(sus)} (V) Min.	V _{CE} (V) Min.	h _{FE} Min./Max.	@ I _c (A)	Resistive Switching			f _r (MHz) Min.	P _o (Case) Watts @ 25°C
NPN	PNP						t _s (μs) Max.	t _t (μs) Max.	@ I _c (A)		
MUF122 ²	MUF127 ²	5	100	—	2000 Min.	3.0	1.5 Typ.	1.50 Typ.	3.0	4 ¹	28
MUF44H11	MUF45H11	10	80	—	40/100	4.0	0.5 Typ.	0.14 Typ.	5.0	40	35
MUF638 ²	MUF668 ²	10	100	—	3 K/20 K	3.0	1.5 Typ.	1.50 Typ.	—	20 ¹	40

¹I_hl @ 1 MHz. ²Darlington. ³Switching tests performed with special application simulator circuit. See data sheet for details.

Plastic TO-220

Pin: 1 — Base, 2 — Collector, 3 — Emitter (Style 1, Case 221A-06)

Mfr.'s Type		I _c Cont (A) Max.	V _{CEO(sus)} (V) Min.	h _{FE} Min./Max.	@ I _c (A)	Resistive Switching			f _r (MHz) Min.	P _o (Case) Watts @ 25°C
NPN	PNP					t _s (μs) Max.	t _t (μs) Max.	@ I _c (A)		
TIP29B	—	1	80	15/75	1.0	0.6 Typ.	0.30 Typ.	1.0	3.0	30
TIP29C	TIP30C	1	100	15/75	1.0	0.6 Typ.	0.30 Typ.	1.0	3.0	30
TIP47	—	1	250	30/150	0.3	2.0 Typ.	0.18 Typ.	0.3	10.0	40
TIP48	—	1	300	30/150	0.3	2.0 Typ.	0.18 Typ.	0.3	10.0	40
—	MJE5731	1	350	30/150	0.3	2.0 Typ.	0.18 Typ.	0.3	10.0	40
TIP50	—	1	400	30/150	0.3	2.0 Typ.	0.18 Typ.	0.3	10.0	40
TIP110 ²	TIP115 ²	2	60	500 Min.	2.0	1.7 Typ.	1.30 Typ.	2.0	25.0 ¹	50
—	TIP115 ²	2	80	500 Min.	2.0	1.7 Typ.	1.30 Typ.	2.0	25.0 ¹	50
TIP112 ^{2,4}	TIP117 ^{2,4}	—	100	500 Min.	2.0	1.7 Typ.	1.30 Typ.	2.0	25.0 ¹	50
BUX85	—	2	450/1000	30	0.1	3.5	1.40	1.0	4.0	50
MJE1320	—	2	900/1800	3 Min.	1.0	4.0 Typ.	0.80 Typ.	1.0	—	80
TIP31A	TIP32A	3	60	25 Min.	1.0	0.6 Typ.	0.30 Typ.	1.0	3.0	40
—	TIP32B	3	80	25 Min.	1.0	0.6 Typ.	0.30 Typ.	1.0	3.0	40
TIP31C ²	TIP32C ²	3	100	25 Min.	1.0	0.6 Typ.	0.30 Typ.	1.0	3.0	40
MJE13005	—	4	400/700	6/30	3.0	0.7	0.70	3.0	4.0	60
TIP120 ²	TIP125 ²	5	60	1 K Min.	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	65
TIP121 ²	TIP126 ²	5	80	1 K Min.	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	65
TIP122 ^{2,4}	TIP127 ^{2,4}	5	100	1 K Min.	3.0	1.5 Typ.	1.50 Typ.	4.0	4.0 ¹	75
MJE18204	—	5	450/1000	14/36	1.0	3.0	0.50	2.5	12.0 ¹	100
TIP41C	TIP42A	6	60	15/75	3.0	0.4 Typ.	0.15 Typ.	3.0	3.0	65
TIP42C	—	6	100	15/75	3.0	0.4 Typ.	0.15 Typ.	3.0	3.0	65
—	2N6109	7	50	30/150	2.5	0.4 Typ.	0.15 Typ.	3.0	4.0	40
2N6292	2N6107	7	70	30/150	2.5	0.4 Typ.	0.15 Typ.	3.0	4.0	40
2N6043 ²	2N6040 ²	8	80	1 K/10 K	4.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	75
TIP100 ²	TIP105 ²	8	60	1 K/20 K	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	80
TIP101 ²	TIP106 ²	8	80	1 K/20 K	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	75
2N6042 ²	2N6042 ²	8	100	1 K/10 K	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	75
TIP102 ²	TIP107 ²	8	100	1 K/20 K	3.0	1.5 Typ.	1.50 Typ.	3.0	4.0 ¹	80
MJE15028	MJE15029	8	120	20 Min.	4.0	—	—	3.0	50	50
MJE15030	MJE15031	8	150	20 Min.	4.0	—	—	3.0	50	50
MJE5740 ²	—	8	300/600	200 Min.	4.0	8.0 Typ.	2.00 Typ.	6.0	4.0	80
MJE5742 ²	MJE5851	8	350	15 Min.	2.0	2.0	0.50	4.0	—	80
MJE13007 ²	—	8	400/700	200 Min.	4.0	8.0 Typ.	2.00 Typ.	6.0	12.0 Typ.	80
—	MJE5852 ²	8	400/700	5/30	5.0	3.0	0.70	5.0	12.0 Typ.	80
D44H8	D45H8	10	60	40 Min.	4.0	—	—	—	50	50
MJE3057T	MJE295T	10	60	20/70	4.0	—	—	—	75	75
2N6387 ²	2N6667 ²	10	60	1 K/20 K	5.0	—	—	20.0 ¹	65	65
D44H11 ²	D45H11 ²	10	80	40 Min.	4.0	0.5 Typ.	0.14 Typ.	5.0	50.0 Typ.	50
2N6487	—	15	60	20/150	5.0	0.6 Typ.	0.30 Typ.	5.0	5.0	75
2N6488	2N6491	15	80	20/150	5.0	0.6 Typ.	0.30 Typ.	5.0	5.0	75
D44VH10	D45VH10	15	80	20 Min.	4.0	0.5	0.09	8.0	50.0 Typ.	83

Plastic TO-218 Type Pin: 1 — Base, 2 — Collector, 3 — Emitter, 4 — Collector (Style 1, Case 340D-01 (TO-218 Type, SOT-93))

Mfr.'s Type		I _c Cont (A) Max.	V _{CEO(sus)} (V) Min.	V _{CE} (V) Min.	h _{FE} Min./Max.	@ I _c (A)	Resistive Switching			f _r (MHz) Min.	P _o (Case) Watts @ 25°C
NPN	PNP						t _s (μs) Max.	t _t (μs) Max.	@ I _c (A)		
TIP140 ²	TIP145 ²	10	60	500 Min.	10.0	2.5 Typ.	2.50 Typ.	5.0	4.0 ¹	125	
TIP141 ²	TIP146 ²	10	80	500 Min.	10.0	2.5 Typ.	2.50 Typ.	5.0	4.0 ¹	125	
TIP142 ²	—	10	100	500 Min.	10.0	2.5 Typ.	2.50 Typ.	5.0	4.0 ¹	125	
TIP3055	TIP2955	15	60	5 Min.	10.0	—	—	—	2.5	80	
MJH11020 ²	MJH11021 ²	15	200	400/15 K	10.0	—	—	—	3.0 ¹	150	
MJH11022 ²	MJH11021 ^{2</sup}										