

MH
KTB MH 916120 S4E0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Stainless steel housings for the use within explosive-risk zones

The Klippon® TB housing series features excellent performance characteristics, even under the most difficult environmental surroundings. And it meets the stricter requirements of explosive-risk zones found in the process or power generation industries

The new Klippon® TB MH housing series offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH housing series features the following advantages:

- Available in 12 sizes and 3 standard depths
- Equipped with up to 4 flange plates
- The seal is protected against compression
- Completely removable padlock mechanism
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable cover – no tools required
- Earth stud in housing cover and bottom section
- Welded-on mounting feet
- International approvals

General ordering data

Order No.	1195550000
Type	KTB MH 916120 S4E0
Version	Enclosures, stainless steel enclosure, Stainless steel 1.4404 (316L), 914 mm, 200 mm, 610 mm
GTIN (EAN)	4032248978199
Qty.	1 pc(s).

MH

KTB MH 916120 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	200 mm	Width	610 mm
Height	914 mm	Depth	200 mm
Mounting dimension - width	636 mm	Mounting dimension - height	559 mm
Net weight	19,600 g		

Cable glands, left

M12 (3)	116	M16 (3)	80
M20 (3)	52	M25 (3)	42
M32 (3)	24	M40 (3)	20
M50 (3)	8	M63 (3)	6
M75 (3)	6		

Cable glands, right

M12 (2)	116	M16 (2)	80
M20 (2)	52	M25 (2)	42
M32 (2)	24	M40 (2)	20
M50 (2)	8	M63 (2)	6
M75 (2)	6		

Cable glands, top/bottom

M12	88	M16	58
M20	38	M25	33
M32	18	M40	15
M50	6	M63	5
M75	4		

General information

AF size 1	10 mm	Access opening: height	861 mm
Access opening: width		Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore
	551 mm	Material thickness	1.5 mm
Installation advice	Terminal rail / mounting plate	Material thickness of flange	3 mm
Material thickness of cover	1.5 mm	Opening angle lid	125 °
Max. payload	223 kg	Position PE bolts	Page C
Overall dimensions	914 x 661 x 215	Seal material	Silicone
Material	Stainless steel 1.4404 (316L)	Operating temperature, min.	-60 °C
Surface finish	electropolished	Impact resistance	7 J ATEX version, 10 J version standard
Operating temperature, max.	135 °C	Note: protection class	For use in the temperature range over 105°C, the IP protection is limited to IP 66.
Protection degree		Cover attachment	4 hinges and M6 hex-head slotted screws SW10
	IP 66, IP 67		
Enclosure attachment	4 welded-on mounting feet with 11-mm holes (2 slotted feet and 2 cross- shaped feet)		
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread		

Creation date April 25, 2013 10:15:32 PM CEST

MH

KTB MH 916120 S4E0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Housing earth

Earth, housing, internal	Welded-on M6 stainless-steel earth stud in lower part of housing and lid.
--------------------------	---

horizontal assembly

WDU 10 / ZDU 10	6x52	WDU 16 / ZDU 16	5x43
WDU 2,5 / ZDU 2,5 / IDU 2,5	8x102	WDU 35 / ZDU 35	4x32
WDU 4 / ZDU 4	7x85	WDU 6 / ZDU 6	7x64

vertical assembly

WDU 10 / ZDU 10 (2)	3x82	WDU 16 / ZDU 16 (2)	3x68
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	5x161	WDU 35 / ZDU 35 (2)	2x51
WDU 4 / ZDU 4 (2)	4x135	WDU 6 / ZDU 6 (2)	4x102

Classifications

eClass 6.2	27-14-91-07	eClass 7.1	27-14-91-07
------------	-------------	------------	-------------

Test certificates

Certificate No. (ATEX)	KEMA10ATEX0046U	Certificate No. (GERMLLOYD)	11533-10
Certificate No. (IECEX)	IECEXKEM10.0015U	Certificate No. (MARITREG)	10.04093.250
Certificate no. (cULus)	E243298VOL1SEC4		

Approvals

Approvals



MH
KTB MH 916120 S4E0

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

