





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



RECOMMENDED P.C.B LAYOUT
(TOLERANCE ± 0.03)

Customer Drawing

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1			07/13/08	

D-SUB TECHNICAL DATA

SHELL :Steel 2.5um (100u") min tin over 1.25um (50u") min nickel

BODY : Glass filled thermoplastic.

Flame retardant to UL94 V-0 Color Black

CONTACTS : Copper alloy.

gold flash over 1.25um (50u") min nickel

ELECTRICAL : Voltage rating : 1000 V RMS at 50 Hz

Current rating 3A.

Insulation resistance >5000 M Ohms

Contact resistance 20 mOhms max.

CLIMATIC : Temperature range -55°C to 125°C


Damp heat 56 days(40°C -95% HR)

MARKING : Amphenol...(Series No.)

Commercial reference

Manufacturing date

PRODUCT CODE



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE	Amphenol [®]
U.S.	METRIC	DRAWN	Christine	07/13/08	
.X +/-	0.50	CHECKED	lik.wang	07/13/08	
.XX +/-	0.30	CHECKED			
.XXX +/-	0.20				TITLE Stamped contacts connector, SD series
FRACTIONS +/-		DRAWING FILE :			
ANGLES +/-	2'	ANGLE OF PROJECTION			
REMOVE SHARP EDGES		SCALE			
DIMENSIONS		SIZE			DRAWING NO. C L77SDD50SOL2
U.S.	INCHES	A4			
METRIC	MM	SCALE NONE			
SHEET 1 OF 1					REV. 1