

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	F	REV AND REDRAWN PER EC 0L30-0001-96		9-12-96	JH	RS	

1. WIRE RANGE: 12-10 (3-6mm²) AWG
INSULATION RANGE: .185 MAX.



.050	1.27	.156	3.96	.245	6.22		
.043	1.09	.155	3.94	.230	5.84		
.035	0.89	.152	3.86	.215	5.46		
.018	0.46	.148	3.76	.185	4.70	.770	19.56
.015	0.38	.135	3.43	.175	4.45	.750	19.05
.005	0.13	.063	1.60	.160	4.06	.259	6.58
IN	MM	IN	MM	IN	MM	IN	MM

CONVERSION TABLE



TIN	.018 BRASS	61233-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. HUFFMAN 9-12-96	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK R. SWING 9-12-96		
		APVD C. MARTIN 9-12-96	NAME SOCKET, .156 MATE-N-LOK™	
		PRODUCT SPEC	SIZE A2	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLY SPEC	CAGE CODE 00779	
0 PLC ±-		—	DRAWING NO C-61233	
1 PLC ±-		—	SCALE 5:1	
2 PLC ±-		—	SHEET 1 OF 1	
3 PLC ±.005		—	REV F	
4 PLC ±-		—		
ANGLES ±-		—		
FINISH SEE TABLE		WEIGHT —		
		CUSTOMER DRAWING		