

D8LD40

400V 8A

FEATURES

- Low noise
- trr50ns
- Fully Isolated Molding

APPLICATION

- Switching power supply
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

RATINGS


●Absolute Maximum Ratings (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		400	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load, Rating for each diode IO/2, Tc=114°C	8	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	60	A
Dielectric Strength	Vdis	Terminals to case, AC 1 minute	1.5	kV
Mounting Torque	TOR	(Recommended torque: 0.3N·m)	0.5	N·m

●Electrical Characteristics (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=4A, Pulse measurement, Rating of per diode	Max 1.3	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max 10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A, Rating of per diode	Max 50	ns
Thermal Resistance	θjc	junction to case	Max 3.3	°C/W
	θjf	junction to heatsink (Reference value)	Max 4.8	

OUTLINE DIMENSIONS




D8LD40

Forward Voltage




D8LD40

Forward Power Dissipation




$$T_j = T_{jmax}$$




D8LD40

Derating Curve




$$V_R = V_{RM}$$



D8LD40

Peak Surge Forward Capability



D8LD40 Junction Capacitance

