

6

5

4

3

2

1

MATERIAL AND FINISH:

Insulator: Nylon 66, black, UL-94V-1 rated

Contacts: Brass, Tin plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A

Voltage rating: 250 VAC

Current rating: 15 A

Voltage rating: 250 VAC

Insulation resistance: 100 Mohm min. at 500 VDC



Dielectric withstanding voltage: 2000 VAC for one minute

Operating Temperature: 70°C



**RoHS
COMPLIANT**

NOTES:

Recommended panel thickness
0.8mm max. to 3.5mm max.



RECOMMENDED
PANEL CUTOUT



REVISIONS

REV	DATE	CHANGE	CHNG	CHK	APPR
A	10/24/01	REVISED / REDRAWN	GQ	TD	PB
B	12/6/05	PANEL CUTOUT DIM A	PB		

PANEL THICKNESS	A
0.8 - 1.2	20.3
1.3 - 2.0	20.5

TOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20

DRAWN BY	SS	DATE:	04/17/00
CHECK BY	PB	DATE:	4/17/00
APPR BY	SS	DATE:	4/17/00

Power Dynamics, Inc.

Phone: 973 560-0019 Whippary, New Jersey Fax: 973 560-0076

PART: UNIVERSAL IEC 60320 C14 APPL. INLET;
SOLDER TERMINALS, SNAP-IN

PART #: PD-42R03-11

SIZE: A

SCALE: NTS

ALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERS

SHEET
1 of 1

REV: B