


## C4532X5R1C226M230KA

Applications		Commercial Grade
Feature	<b>General</b>	General (Up to 50V)
Series	C4532	[EIA CC1812]



Size	
Length(L)	4.50mm +/-0.40mm
Width(W)	3.20mm +/-0.40mm
Thickness(T)	2.30mm +/-0.20mm
Terminal Width(B)	0.20mm Min.
Terminal Spacing(G)	

Electrical Characteristics	
Capacitance	22uF +/-20%
Rated Voltage	16Vdc
Temperature Characteristic	X5R(+/-15%)
Dissipation Factor	7.5% Max.
Insulation Resistance	4M Min.






Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	500 Pcs Min.

•This PDF document was created based on the data listed on the TDK Corporation website.

•All specifications are subject to change without notice.

C4532X5R1C226M230KA

## Characteristic Graphs



•This PDF document was created based on the data listed on the TDK Corporation website.

•All specifications are subject to change without notice.