



MUR820 THRU MUR860

8.0 AMPS. Ultrafast Plastic Rectifiers



Voltage Range
200 to 600 Volts
Current
8.0 Amperes



Features

- ✧ Low forward voltage drop
- ✧ High current capability
- ✧ High reliability
- ✧ High surge current capability

Mechanical Data

- ✧ Cases: to-220a molded plastic
- ✧ Epoxy: UL 94V-0 rate flame retardant
- ✧ Terminals: Leads, solderable per MIL-STD-202, Method 208 guaranteed
- ✧ Polarity: As marked
- ✧ High temperature soldering guaranteed: 260°C/10 seconds/.25"(.635mm) from case.
- ✧ Weight: 2.24 grams

TO-220A



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	MUR820	MUR840	MUR860	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	200	400	600	V
Maximum RMS Voltage	V _{RMS}	140	280	420	V
Maximum DC Blocking Voltage	V _{DC}	200	400	600	V
Maximum Average Forward Rectified Current .375"(9.5mm) Lead Length (See Fig. 1)	I _{AV}	8.0			A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	100			A
Maximum Instantaneous Forward Voltage @ 8.0A	V _F	0.975	1.30	1.7	V
Maximum DC Reverse Current @ T _C =25℃ at Rated DC Blocking Voltage @ T _C =150℃ (Note 4)	I _R	5.0 250			uA uA
Maximum Reverse Recovery Time (Note 2)	T _{rr}	25	50		nS
Typical Thermal Resistance (Note 3)	Rθ _{JC}	3.0	2.0		℃/W
Operating Temperature Range	T _J	-65 to +175			℃
Storage Temperature Range	T _{STG}	-65 to +175			℃

Notes: 1. Measured at 1 MHz and Applied Reverse Voltage of 4..0 Volts D.C.

2. Reverse Recovery Test Conditions: $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{RR}=0.25\text{A}$

3. Thermal Resistance from Junction to Case, Mounted on Heatsink Size of 2" x 3" x 0.25" Al-Plate.

4. Pulse lest: $t_p = 300 \mu\text{s}$, Duty Cycle < 2%.

RATINGS AND CHARACTERISTIC CURVES (MUR820 THRU MUR860)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4- TYPICALS REVERSE CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE PERLEG

