

D-Series

Single Pole Toggle Switches

The D-Series single pole compact high current toggle switches are ideal for applications with back panel size constraints. These switches feature self-cleaning contacts and ratings up to 20A 125VAC, 10A 250VAC, 1 1/2 HP 125-250VAC. With an economical double insulated all nylon construction, these switches figure prominently in the Environmental Controls, Marine, Food Service, Vacuum Cleaner and various other general purpose markets with stringent current carrying requirements.



Carling Technologies®

Innovative Designs. Powerful Solutions.

INNOVATIVE DESIGNS. POWERFUL SOLUTIONS.

Carling Technologies, Inc.
60 Johnson Avenue • Plainville, CT 06062-1177
Phone: (860) 793-9281 • Fax: (860) 793-9231
Email: sales@carlingtech.com • www.carlingtech.com

Dielectric Strength

UL/CSA: 1000V - live to dead
metal parts & opposite polarity
TUV: 4000V - live to dead metal
parts; 750V - across open contacts

Electrical Life


50,000 cycles

Mechanical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0° to 85°C)



1 BASE PART NUMBER: SERIES/CIRCUITRY/RATING¹/TERMINATION

10A 250VAC, 20A 125VAC, 1 1/2 HP 125-250VAC

On-None-Off	Solder Lug	.250 Tab	Wire Leads
On-None-On	DA220	DA221	DA225
On-Off-On	DB220	DB221	DB225
	DC220	DC221	DC225

5A 250VAC, 10A 125VAC, 1/2 HP 125-250VAC,
4(4) 250VAC μ TUV approved

On-None-Off Wire Leads
DA9451

2 ACTUATOR STYLE

B Bat P Paddle

3 ACTUATOR COLOR²


B Black W White




4 BUSHING COLOR²

B Black W White

Notes:

- 1 DA945 available with wire leads and ON-OFF circuit only.
- 2 Additional colors available. Please consult factory.



		
SOLDER LUG	.250 TAB (Q.C.)	INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE		

