





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS



- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 5 NOT CUMULATIVE TOLERANCE.




282826-2 AS SHOWN



125	13	1-282826-3
115	12	1-282826-2
105	11	1-282826-1
95	10	1-282826-0
85	9	282826-9
75	8	282826-8
65	7	282826-7
55	6	282826-6
45	5	282826-5
35	4	282826-4
25	3	282826-3
15	2	282826-2
DIM. A		N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 31 JUL 2001	TE Connectivity			
DIMENSIONS: mm		CHK D. BIEVENOUR 31 JUL 2001				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 31 JUL 2001	NAME TERMINAL BLOCK HEADER ASSEMBLY 180 DEGREE CLOSED ENDS 10mm PITCH			
0 PLC ±.3 1 PLC ±.25 2 PLC ±.25 3 PLC ±. 4 PLC ±. ANGLES ±2		PRODUCT SPEC 108-20166	SIZE A3			
MATERIAL		APPLICATION SPEC 114-20079	CAGE CODE 00779			
FINISH		WEIGHT -	DRAWING NO C-282826			
CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1		REV C1