

Typical Applications:

- Fax: (321) 637-1600 Web Site: www.rencousa.com E-mail: sales@rencousa.com

RL-1256-1					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms) (DC Amps)	Saturation Current	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-1-1.0	1.0	.003	87.0	9.0	.550
RL-1256-1-1.2	1.2	.003	68.0	9.0	.550
RL-1256-1-1.5	1.5	.004	56.0	9.0	.550
RL-1256-1-1.8	1.8	.004	56.0	9.0	.550
RL-1256-1-2.2	2.2	.005	47.0	9.0	.550
RL-1256-1-2.7	2.7	.005	47.0	9.0	.550
RL-1256-1-3.3	3.3	.005	40.0	9.0	.550
RL-1256-1-3.9	3.9	.006	36.0	9.0	.550
RL-1256-1-4.7	4.7	.007	32.0	9.0	.550
RL-1256-1-5.6	5.6	.007	29.0	9.0	.550
RL-1256-1-6.8	6.8	.008	26.0	9.0	.550
RL-1256-1-8.2	8.2	.009	24.5	9.0	.550
RL-1256-1-10	10.0	.010	21.2	9.0	.550
RL-1256-1-12	12.0	.011	19.0	9.0	.550
RL-1256-1-15	15.0	.015	17.5	7.2	.500
RL-1256-1-18	18.0	.016	16.5	7.2	.500
RL-1256-1-22	22.0	.025	15.8	5.5	.500
RL-1256-1-27	27.0	.030	14.4	4.5	.500
RL-1256-1-33	33.0	.040	13.2	4.0	.406
RL-1256-1-39	39.0	.046	11.8	4.0	.469
RL-1256-1-47	47.0	.062	11.0	2.8	.469
RL-1256-1-56	56.0	.069	10.0	2.8	.485
RL-1256-1-68	68.0	.077	8.9	2.8	.500
RL-1256-1-82	82.0	.083	8.2	2.8	.500
RL-1256-1-100	100.0	.095	7.5	2.8	.500
RL-1256-1-120	120.0	.127	5.8	2.0	.480
RL-1256-1-150	150.0	.181	5.6	1.6	.480
RL-1256-1-180	180.0	.217	5.1	1.6	.480
RL-1256-1-220	220.0	.240	4.3	1.6	.480
RL-1256-1-270	270.0	.300	4.1	1.6	.480
RL-1256-1-330	330.0	.336	3.8	1.3	.480
RL-1256-1-390	390.0	.460	3.3	1.0	.480
RL-1256-1-470	470.0	.636	3.2	0.8	.450
RL-1256-1-560	560.0	.696	2.9	0.8	.450

NOTES:

1. Saturation current lowers inductance 5%
2. Inductance $\pm 10\%$ measured at 1KHz, values below $10\mu H \pm 20\%$
3. Leads for PC mounting tinned to within 1/16" of body
4. Non-listed values available on request
5. Coils finished with sleeving UL-VW-1 rated
6. Encapsulated to MIL-T-27D available, see Renco RL-1324 Series
7. Center hole for mechanical mounting
8. 1000VAC RMS hi pot
9. RDC measured @ 20°C
10. Spacer available at additional cost to facilitate PC board washing



SINCE 1955

RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com

RL-1256-2					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms)	Saturation Current (DC Amps)	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-2-1.0	1.0	.003	108.0	11.4	.620
RL-1256-2-1.2	1.2	.003	108.0	11.4	.620
RL-1256-2-1.5	1.5	.003	83.0	11.4	.620
RL-1256-2-1.8	1.8	.003	68.0	11.4	.620
RL-1256-2-2.2	2.2	.004	68.0	11.4	.620
RL-1256-2-2.7	2.7	.005	58.0	11.4	.620
RL-1256-2-3.3	3.3	.005	58.0	11.4	.620
RL-1256-2-3.9	3.9	.005	50.0	11.4	.620
RL-1256-2-4.7	4.7	.005	50.0	11.4	.620
RL-1256-2-5.6	5.6	.006	44.0	11.4	.620
RL-1256-2-6.8	6.8	.007	39.0	11.4	.620
RL-1256-2-8.2	8.2	.007	36.0	11.4	.620
RL-1256-2-10	10.0	.009	30.0	11.4	.620
RL-1256-2-12	12.0	.009	27.0	11.4	.620
RL-1256-2-15	15.0	.013	25.0	9.0	.625
RL-1256-2-18	18.0	.018	22.0	7.2	.630
RL-1256-2-22	22.0	.019	21.0	7.2	.630
RL-1256-2-27	27.0	.026	20.5	5.5	.546
RL-1256-2-33	33.0	.029	18.6	5.5	.546
RL-1256-2-39	39.0	.030	17.0	5.5	.594
RL-1256-2-47	47.0	.035	15.1	5.5	.625
RL-1256-2-56	56.0	.039	13.6	5.5	.625
RL-1256-2-68	68.0	.053	12.7	4.8	.656
RL-1256-2-82	82.0	.060	11.3	4.8	.656
RL-1256-2-100	100.0	.080	10.4	4.0	.593
RL-1256-2-120	120.0	.090	9.4	4.0	.593
RL-1256-2-150	150.0	.098	8.6	4.0	.593
RL-1256-2-180	180.0	.110	7.8	4.0	.671
RL-1256-2-220	220.0	.150	7.0	2.8	.593
RL-1256-2-270	270.0	.213	6.3	2.0	.562
RL-1256-2-330	330.0	.305	5.2	1.6	.590
RL-1256-2-390	390.0	.320	4.9	1.6	.590
RL-1256-2-470	470.0	.355	4.5	1.6	.590
RL-1256-2-560	560.0	.388	4.1	1.6	.590
RL-1256-2-680	680.0	.430	3.7	1.6	.590
RL-1256-2-820	820.0	.590	3.4	1.3	.590
RL-1256-2-1000	1000.0	.818	3.1	1.0	.590
RL-1256-2-1200	1200.0	1.14	2.7	0.8	.590
RL-1256-2-1500	1500.0	1.26	2.4	0.8	.590
RL-1256-2-1800	1800.0	1.39	2.2	0.8	.590
RL-1256-2-2200	2200.0	1.54	2.0	0.8	.590



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com 📧 E-mail: sales@rencousa.com

RL-1256-3					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms) (DC Amps)	Saturation Current	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-3-1.0	1.0	.003	116.0	21.0	.800
RL-1256-3-1.2	1.2	.003	116.0	21.0	.800
RL-1256-3-1.5	1.5	.003	116.0	21.0	.800
RL-1256-3-1.8	1.8	.003	90.0	21.0	.800
RL-1256-3-2.2	2.2	.003	90.0	21.0	.800
RL-1256-3-2.7	2.7	.003	74.0	21.0	.800
RL-1256-3-3.3	3.3	.003	74.0	21.0	.800
RL-1256-3-3.9	3.9	.003	62.0	21.0	.800
RL-1256-3-4.7	4.7	.003	54.0	21.0	.800
RL-1256-3-5.6	5.6	.003	54.0	21.0	.800
RL-1256-3-6.8	6.8	.004	47.0	21.0	.800
RL-1256-3-8.2	8.2	.004	42.0	21.0	.800
RL-1256-3-10	10.0	.006	38.0	17.0	.700
RL-1256-3-12	12.0	.008	35.0	13.5	.690
RL-1256-3-15	15.0	.009	32.0	13.5	.690
RL-1256-3-18	18.0	.010	29.0	13.5	.690
RL-1256-3-22	22.0	.011	25.0	13.5	.790
RL-1256-3-27	27.0	.012	23.0	13.5	.790
RL-1256-3-33	33.0	.017	20.0	13.5	.790
RL-1256-3-39	39.0	.022	19.1	11.4	.790
RL-1256-3-47	47.0	.024	19.0	9.0	.750
RL-1256-3-56	56.0	.026	17.5	9.0	.750
RL-1256-3-68	68.0	.029	15.6	9.0	.750
RL-1256-3-82	82.0	.032	14.0	9.0	.750
RL-1256-3-100	100.0	.034	13.2	9.0	.781
RL-1256-3-120	120.0	.046	12.1	7.2	.750
RL-1256-3-150	150.0	.064	10.8	5.5	.781
RL-1256-3-180	180.0	.072	9.7	5.5	.781
RL-1256-3-220	220.0	.080	8.7	5.5	.781
RL-1256-3-270	270.0	.110	7.9	4.5	.750
RL-1256-3-330	330.0	.122	7.1	4.5	.812
RL-1256-3-390	390.0	.169	6.7	4.0	.750
RL-1256-3-470	470.0	.187	6.0	4.0	.750
RL-1256-3-560	560.0	.205	5.5	4.0	.750
RL-1256-3-680	680.0	.256	5.0	2.8	.718
RL-1256-3-820	820.0	.288	4.5	2.8	.843
RL-1256-3-1000	1000.0	.426	4.1	2.0	.750
RL-1256-3-1200	1200.0	.462	3.7	2.0	.750
RL-1256-3-1500	1500.0	.518	3.4	2.0	.750
RL-1256-3-1800	1800.0	.705	2.8	1.6	.770
RL-1256-3-2200	2200.0	1.02	2.5	1.3	.770
RL-1256-3-2700	2700.0	1.14	2.3	1.3	.770
RL-1256-3-3300	3300.0	1.27	2.0	1.3	.750
RL-1256-3-3900	3900.0	1.67	1.8	1.0	.750
RL-1256-3-4700	4700.0	1.86	1.7	1.0	.750



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com 📧 E-mail: sales@rencousa.com

RL-1256-4					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms)	Saturation Current (DC Amps)	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-4-1.8	1.8	.002	150.0	27.0	1.11
RL-1256-4-2.2	2.2	.002	150.0	27.0	1.11
RL-1256-4-2.7	2.7	.003	115.0	27.0	1.11
RL-1256-4-3.3	3.3	.003	115.0	27.0	1.11
RL-1256-4-3.9	3.9	.003	95.0	27.0	1.11
RL-1256-4-4.7	4.7	.003	95.0	27.0	1.11
RL-1256-4-5.6	5.6	.004	79.0	27.0	1.11
RL-1256-4-6.8	6.8	.004	79.0	27.0	1.11
RL-1256-4-8.2	8.2	.004	69.0	27.0	1.11
RL-1256-4-10	10.0	.005	61.0	27.0	1.11
RL-1256-4-12	12.0	.005	55.0	27.0	1.11
RL-1256-4-15	15.0	.006	49.0	27.0	1.11
RL-1256-4-18	18.0	.008	41.0	27.0	1.11
RL-1256-4-22	22.0	.009	38.0	21.0	1.11
RL-1256-4-27	27.0	.010	36.0	21.0	1.15
RL-1256-4-33	33.0	.011	31.0	21.0	1.15
RL-1256-4-39	39.0	.012	28.0	21.0	1.15
RL-1256-4-47	47.0	.018	27.0	14.4	1.140
RL-1256-4-56	56.0	.019	26.1	14.4	1.140
RL-1256-4-68	68.0	.021	24.4	14.4	1.140
RL-1256-4-82	82.0	.023	22.4	14.4	1.140
RL-1256-4-100	100.0	.025	20.0	14.4	1.140
RL-1256-4-120	120.0	.028	18.0	14.4	1.187
RL-1256-4-150	150.0	.040	16.4	11.4	1.125
RL-1256-4-180	180.0	.045	14.6	11.4	1.125
RL-1256-4-220	220.0	.050	13.2	11.4	1.125
RL-1256-4-270	270.0	.056	11.8	11.4	1.156
RL-1256-4-330	330.0	.074	11.4	11.4	1.125
RL-1256-4-390	390.0	.082	10.1	9.0	1.187
RL-1256-4-470	470.0	.114	9.2	7.2	1.125
RL-1256-4-560	560.0	.125	8.3	7.2	1.125
RL-1256-4-680	680.0	.139	7.6	7.2	1.125
RL-1256-4-820	820.0	.154	6.8	7.2	1.187
RL-1256-4-1000	1000.0	.216	6.2	5.5	1.062
RL-1256-4-1200	1200.0	.232	5.7	5.5	1.156
RL-1256-4-1500	1500.0	.324	5.1	4.5	1.156
RL-1256-4-1800	1800.0	.360	4.6	4.5	1.156
RL-1256-4-2200	2200.0	.494	4.2	4.0	1.062
RL-1256-4-2700	2700.0	.555	3.8	4.0	1.062
RL-1256-4-3300	3300.0	.773	3.4	2.8	1.062
RL-1256-4-3900	3900.0	.845	3.1	2.8	1.125
RL-1256-4-4700	4700.0	1.14	2.9	2.0	1.11
RL-1256-4-5600	5600.0	1.60	2.5	2.0	1.11
RL-1256-4-6800	6800.0	1.76	2.3	1.6	1.11
RL-1256-4-8200	8200.0	1.95	2.0	1.6	1.16
RL-1256-4-10000	10000.0	2.76	1.8	1.3	1.16
RL-1256-4-12000	12000.0	3.04	1.7	1.3	1.16
RL-1256-4-15000	15000.0	3.39	1.5	1.3	1.16



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com

RL-1256-5					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms) (DC Amps)	Saturation Current	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-5-1.8	1.8	.002	155.0	35.0	1.11
RL-1256-5-2.2	2.2	.002	155.0	35.0	1.11
RL-1256-5-2.7	2.7	.002	125.0	35.0	1.11
RL-1256-5-3.3	3.3	.002	125.0	35.0	1.11
RL-1256-5-3.9	3.9	.003	102.0	35.0	1.11
RL-1256-5-4.7	4.7	.003	87.0	35.0	1.11
RL-1256-5-5.6	5.6	.003	87.0	35.0	1.11
RL-1256-5-6.8	6.8	.003	87.0	35.0	1.11
RL-1256-5-8.2	8.2	.003	76.0	35.0	1.11
RL-1256-5-10	10.0	.004	67.0	35.0	1.11
RL-1256-5-12	12.0	.004	60.0	35.0	1.16
RL-1256-5-15	15.0	.005	49.0	35.0	1.16
RL-1256-5-18	18.0	.007	45.0	27.0	1.16
RL-1256-5-22	22.0	.007	42.0	27.0	1.16
RL-1256-5-27	27.0	.008	35.0	27.0	1.16
RL-1256-5-33	33.0	.009	34.0	27.0	1.16
RL-1256-5-39	39.0	.010	30.0	27.0	1.16
RL-1256-5-47	47.0	.011	28.0	27.0	1.16
RL-1256-5-56	56.0	.013	26.0	21.0	1.16
RL-1256-5-68	68.0	.015	23.0	21.0	1.25
RL-1256-5-82	82.0	.017	20.0	21.0	1.28
RL-1256-5-100	100.0	.018	19.0	21.0	1.25
RL-1256-5-120	120.0	.022	18.0	17.0	1.16
RL-1256-5-150	150.0	.025	16.0	17.0	1.16
RL-1256-5-180	180.0	.035	14.0	13.5	1.10
RL-1256-5-220	220.0	.040	13.0	13.5	1.10
RL-1256-5-270	270.0	.044	11.0	13.5	1.10
RL-1256-5-330	330.0	.049	10.0	13.5	1.11
RL-1256-5-390	390.0	.070	9.7	11.4	1.15
RL-1256-5-470	470.0	.078	8.8	11.4	1.07
RL-1256-5-560	560.0	.105	8.1	9.0	1.07
RL-1256-5-680	680.0	.115	7.4	9.0	1.07
RL-1256-5-820	820.0	.127	6.7	9.0	1.12
RL-1256-5-1000	1000.0	.176	6.1	7.2	1.12
RL-1256-5-1200	1200.0	.195	5.5	7.2	1.12
RL-1256-5-1500	1500.0	.274	5.0	5.5	1.12
RL-1256-5-1800	1800.0	.302	4.5	5.5	1.13
RL-1256-5-2200	2200.0	.338	4.1	5.5	1.16
RL-1256-5-2700	2700.0	.459	3.7	4.5	1.02
RL-1256-5-3300	3300.0	.642	3.4	4.0	1.02
RL-1256-5-3900	3900.0	.699	3.0	4.0	1.14
RL-1256-5-4700	4700.0	.775	2.8	4.0	1.14
RL-1256-5-5600	5600.0	.843	2.6	4.0	1.14
RL-1256-5-6800	6800.0	1.15	2.3	2.8	1.06
RL-1256-5-8200	8200.0	1.26	2.1	2.8	1.16
RL-1256-5-10000	10000.0	1.74	1.9	2.0	1.13
RL-1256-5-12000	12000.0	1.92	1.7	2.0	1.13
RL-1256-5-15000	15000.0	2.17	1.5	2.0	1.13



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

☎ Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com

RL-1256-6					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms) (DC Amps)	Saturation Current	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-6-4.7	4.7	.002	149.9	35.0	1.40
RL-1256-6-5.6	5.6	.002	122.7	35.0	1.40
RL-1256-6-6.8	6.8	.003	103.8	35.0	1.40
RL-1256-6-8.2	8.2	.003	90.0	35.0	1.40
RL-1256-6-10	10.0	.003	79.4	35.0	1.48
RL-1256-6-12	12.0	.004	71.0	35.0	1.48
RL-1256-6-15	15.0	.004	64.3	35.0	1.48
RL-1256-6-18	18.0	.005	58.7	35.0	1.48
RL-1256-6-22	22.0	.005	54.0	35.0	1.48
RL-1256-6-27	27.0	.006	50.0	35.0	1.48
RL-1256-6-33	33.0	.006	46.5	35.0	1.48
RL-1256-6-39	39.0	.006	43.5	35.0	1.48
RL-1256-6-47	47.0	.008	40.9	35.0	1.48
RL-1256-6-56	56.0	.009	36.5	35.0	1.48
RL-1256-6-68	68.0	.009	32.9	35.0	1.48
RL-1256-6-82	82.0	.010	30.0	35.0	1.48
RL-1256-6-100	100.0	.014	26.5	27.0	1.53
RL-1256-6-120	120.0	.015	24.5	27.0	1.53
RL-1256-6-150	150.0	.023	21.4	21.0	1.49
RL-1256-6-180	180.0	.025	19.5	21.0	1.49
RL-1256-6-220	220.0	.028	18.0	21.0	1.49
RL-1256-6-270	270.0	.030	16.2	21.0	1.49
RL-1256-6-330	330.0	.040	14.8	17.0	1.31
RL-1256-6-390	390.0	.055	13.6	13.5	1.31
RL-1256-6-470	470.0	.061	12.3	13.5	1.31
RL-1256-6-560	560.0	.068	11.3	13.5	1.40
RL-1256-6-680	680.0	.094	10.3	11.4	1.42
RL-1256-6-820	820.0	.104	9.4	11.4	1.42
RL-1256-6-1000	1000.0	.143	8.5	9.0	1.36
RL-1256-6-1200	1200.0	.156	7.7	9.0	1.36
RL-1256-6-1500	1500.0	.219	6.8	7.2	1.31
RL-1256-6-1800	1800.0	.241	6.3	7.2	1.31
RL-1256-6-2200	2200.0	.270	5.7	7.2	1.40
RL-1256-6-2700	2700.0	.364	5.1	5.5	1.36
RL-1256-6-3300	3300.0	.498	4.6	4.5	1.24
RL-1256-6-3900	3900.0	.548	4.2	4.5	1.32
RL-1256-6-4700	4700.0	.608	3.9	4.5	1.32
RL-1256-6-5600	5600.0	.671	3.5	4.5	1.36
RL-1256-6-6800	6800.0	.750	3.2	4.5	1.40
RL-1256-6-8200	8200.0	1.03	2.9	4.0	1.45
RL-1256-6-10000	10000.0	1.16	2.6	4.0	1.45
RL-1256-6-12000	12000.0	1.54	2.4	2.8	1.40
RL-1256-6-15000	15000.0	1.75	2.2	2.8	1.40
RL-1256-6-18000	18000.0	1.94	2.0	2.8	1.45
RL-1256-6-22000	22000.0	2.74	1.8	2.0	1.37
RL-1256-6-27000	27000.0	3.71	1.6	1.7	1.37
RL-1256-6-33000	33000.0	4.16	1.5	1.7	1.37
RL-1256-6-39000	39000.0	5.56	1.4	1.4	1.35
RL-1256-6-47000	47000.0	6.19	1.2	1.4	1.35



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com

RL-1256-7					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms)	Saturation Current (DC Amps)	REVISED Rated Current (Amps)	Dimension "E" Approx.
RL-1256-7-5.6	5.6	.0018	200.0	45	1.60
RL-1256-7-6.8	6.8	.0021	163.0	45	1.60
RL-1256-7-8.2	8.2	.0022	163.0	45	1.60
RL-1256-7-10	10.0	.0024	138.0	45	1.60
RL-1256-7-12	12.0	.0025	120.0	45	1.60
RL-1256-7-15	15.0	.0028	105.0	42	1.70
RL-1256-7-18	18.0	.0032	94.0	40	1.70
RL-1256-7-22	22.0	.0036	85.0	38	1.70
RL-1256-7-27	27.0	.0042	78.0	38	1.70
RL-1256-7-33	33.0	.0045	72.0	37	1.70
RL-1256-7-39	39.0	.0048	66.0	36	1.80
RL-1256-7-47	47.0	.0057	58.0	35	1.80
RL-1256-7-56	56.0	.0069	54.0	35	1.80
RL-1256-7-68	68.0	.0078	48.0	35	1.80
RL-1256-7-82	82.0	.0093	43.0	35	1.80
RL-1256-7-100	100.0	.0103	40.0	27	1.80
RL-1256-7-120	120.0	.0108	36.0	27	1.80
RL-1256-7-150	150.0	.0120	32.0	25	1.80
RL-1256-7-180	180.0	.0156	31.0	22	1.80
RL-1256-7-220	220.0	.0168	28.0	22	1.80
RL-1256-7-270	270.0	.0228	24.0	21.0	1.80
RL-1256-7-330	330.0	.0300	23.0	17.0	1.80
RL-1256-7-390	390.0	.0432	21.0	13.5	1.70
RL-1256-7-470	470.0	.0456	19.7	13.5	1.70
RL-1256-7-560	560.0	.0480	17.4	13.5	1.75
RL-1256-7-680	680.0	.0516	15.9	12.0	1.80
RL-1256-7-820	820.0	.0648	14.0	11.5	1.80
RL-1256-7-1000	1000.0	.0936	12.7	10.0	1.75
RL-1256-7-1200	1200.0	.1020	11.9	9.5	1.78
RL-1256-7-1500	1500.0	.1176	10.9	8.0	1.80
RL-1256-7-1800	1800.0	.1536	10.1	7.5	1.70
RL-1256-7-2200	2200.0	.2160	8.9	7.2	1.70
RL-1256-7-2700	2700.0	.2424	8.0	6.0	1.75
RL-1256-7-3300	3300.0	.2640	7.1	5.5	1.80
RL-1256-7-3900	3900.0	.3480	6.8	5.2	1.75
RL-1256-7-4700	4700.0	.3924	6.1	5.0	1.78
RL-1256-7-5600	5600.0	.4320	5.6	4.7	1.80
RL-1256-7-6800	6800.0	.5940	5.0	4.5	1.70
RL-1256-7-8200	8200.0	.6600	4.6	4.0	1.75
RL-1256-7-10000	10000.0	.7560	4.0	4.0	1.80
RL-1256-7-12000	12000.0	.9840	3.7	3.5	1.80
RL-1256-7-15000	15000.0	1.416	3.0	2.8	1.75
RL-1256-7-18000	18000.0	1.524	2.8	2.8	1.78
RL-1256-7-22000	22000.0	1.800	2.7	2.3	1.80
RL-1256-7-27000	27000.0	2.376	2.5	2.0	1.75
RL-1256-7-33000	33000.0	2.640	2.2	1.9	1.80
RL-1256-7-39000	39000.0	3.576	2.1	1.6	1.75
RL-1256-7-47000	47000.0	3.936	1.9	1.6	1.78
RL-1256-7-56000	56000.0	4.320	1.7	1.5	1.80
RL-1256-7-68000	68000.0	5.220	1.5	1.3	1.85



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

📠 Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com

RL-1256-8					
Renco Part No.	Inductance ODC (μH)	Max. DCR (Ohms)	Saturation Current (DC Amps)	Rated Current (Amps)	Dimension "E" Approx.
RL-1256-8-5.6	5.6	.0012	233	55	*
RL-1256-8-6.8	6.8	.0013	197	55	*
RL-1256-8-8.2	8.2	.0015	171	55	*
RL-1256-8-10	10.0	.0017	170	55	*
RL-1256-8-12	12.0	.0020	150	55	*
RL-1256-8-15	15.0	.0021	135	55	*
RL-1256-8-18	18.0	.0023	122	55	*
RL-1256-8-22	22.0	.0025	111	55	*
RL-1256-8-27	27.0	.0026	102	55	*
RL-1256-8-33	33.0	.0029	95.0	55	*
RL-1256-8-39	39.0	.0033	83	55	*
RL-1256-8-47	47.0	.0035	77	55	*
RL-1256-8-56	56.0	.0039	69	55	*
RL-1256-8-68	68.0	.0043	62	50	*
RL-1256-8-82	82.0	.0048	57	45	*
RL-1256-8-100	100.0	.0052	52	40	*
RL-1256-8-120	120.0	.0071	48	39	*
RL-1256-8-150	150.0	.0079	43	38	*
RL-1256-8-180	180.0	.0087	39	37	*
RL-1256-8-220	220.0	.0120	35	33	*
RL-1256-8-270	270.0	.014	32	30	*
RL-1256-8-330	330.0	.018	29	27	1.80
RL-1256-8-390	390.0	.020	27	25	1.70
RL-1256-8-470	470.0	.028	24	21	1.70
RL-1256-8-560	560.0	.031	22	20	1.75
RL-1256-8-680	680.0	.034	20	19	1.80
RL-1256-8-820	820.0	.047	18	16	1.80
RL-1256-8-1000	1000.0	.052	16	15.5	1.75
RL-1256-8-1200	1200.0	.057	15	15	1.78
RL-1256-8-1500	1500.0	.080	13	13	1.80
RL-1256-8-1800	1800.0	.088	12	12	1.70
RL-1256-8-2200	2200.0	.122	11	10	1.70
RL-1256-8-2700	2700.0	.135	10	10	1.75
RL-1256-8-3300	3300.0	.188	9	8	1.80
RL-1256-8-3900	3900.0	.205	8	8	1.75
RL-1256-8-4700	4700.0	.283	7.7	6.7	1.78
RL-1256-8-5600	5600.0	.309	7.0	6.4	1.80
RL-1256-8-6800	6800.0	.431	6.4	5.4	1.70
RL-1256-8-8200	8200.0	.472	5.8	5.2	1.75
RL-1256-8-10000	10000.0	.521	5.2	5.0	1.80
RL-1256-8-12000	12000.0	.717	4.8	4.2	1.80
RL-1256-8-15000	15000.0	.803	4.3	4.0	1.75
RL-1256-8-18000	18000.0	1.111	3.9	3.4	1.78
RL-1256-8-22000	22000.0	1.228	3.5	3.2	1.80
RL-1256-8-27000	27000.0	1.716	3.2	2.7	1.75
RL-1256-8-33000	33000.0	1.896	2.9	2.6	1.80
RL-1256-8-39000	39000.0	2.590	2.6	2.3	1.75
RL-1256-8-47000	47000.0	2.840	2.4	2.2	1.78
RL-1256-8-56000	56000.0	3.104	2.2	2.1	1.80
RL-1256-8-68000	68000.0	4.331	2.0	1.7	1.85
RL-1256-8-82000	82000.0	4.756	1.8	1.6	1.90
RL-1256-8-100000	100000.0	6.652	1.6	1.4	1.95

* Inductors wound with 2 strands of wire. Consult Engineering for dimension.



RENCO ELECTRONICS, INC.

✉ 595 International Place, Rockledge, FL 32955-4200 USA

☎ (321) 637-1000 • Toll Free Engineering Hot line 800-645-5828

☎ Fax: (321) 637-1600 🌐 Web Site: www.rencousa.com ✉ E-mail: sales@rencousa.com