




N-Channel 30-V (D-S) MOSFET with Schottky Diode


MOSFET PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.018 @ $V_{GS} = 10$ V	9
	0.028 @ $V_{GS} = 4.5$ V	7.3

SCHOTTKY PRODUCT SUMMARY		
V_{DS} (V)	V_{SD} (V) Diode Forward Voltage	I_F (A)
30	0.50 V @ 1.0 A	1.4



Ordering Information:

Si4812DY
Si4812DY-T1 (with Tape and Reel)
Si4812DY—E3 (Lead (Pb)-Free)
Si4812DY-T1—E3 (Lead (Pb)-Free with Tape and Reel)



ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C UNLESS OTHERWISE NOTED)					
Parameter		Symbol	Limit		Unit
			10 sec	Steady State	
Drain-Source Voltage (MOSFET)		V _{DS}	30		V
Reverse Voltage (Schottky)			30		
Gate-Source Voltage (MOSFET)		V _{GS}	± 20		
Continuous Drain Current (T _J = 150 °C) (MOSFET) ^{a, b}	T _A = 25 °C	I _D	9	6.9	A
	T _A = 70 °C		7.5	5.6	
Pulsed Drain Current (MOSFET)		I _{DM}	50		
Continuous Source Current (MOSFET Diode Conduction) ^{a, b}		I _S	2.1	1.2	
Average Foward Current (Schottky)		I _F	1.4	0.8	
Pulsed Foward Current (Schottky)		I _{FM}	30		
Maximum Power Dissipation (MOSFET) ^{a, b}	T _A = 25 °C	P _D	2.5	1.4	W
	T _A = 70 °C		1.6	0.9	
Maximum Power Dissipation (Schottky) ^{a, b}	T _A = 25 °C		2.0	1.2	
	T _A = 70 °C		1.3	0.8	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	–55 to 150		°C

THERMAL RESISTANCE RATINGS					
Parameter	Device	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ($t \leq 10$ sec) ^a	MOSFET	R_{thJA}	40	50	$^\circ\text{C/W}$
	Schottky		50	60	
Maximum Junction-to-Ambient ($t = \text{steady state}$) ^a	MOSFET		72	90	
	Schottky		85	100	

Notes

a. Surface Mounted on FR4 Board.

b. $t \leq 10$ sec.

For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>







MOSFET + SCHOTTKY SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	1		3	V
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current (MOSFET + Schottky)	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V		0.004	0.100	mA
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 100°C		0.7	10	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 125°C		3.0	20	
On-State Drain Current ^a	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 10 V	20			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 10 V, I _D = 9 A		0.012	0.018	Ω
		V _{GS} = 4.5 V, I _D = 7.3 A		0.019	0.028	
Forward Transconductance ^a	g _{fs}	V _{DS} = 15 V, I _D = 9 A		23		S
Schottky Diode Forward Voltage ^a	V _{SD}	I _S = 1.0 A, V _{GS} = 0 V		0.45	0.50	V
		I _S = 1.0 A, V _{GS} = 0 V, T _J = 125°C		0.33	0.42	
Dynamic ^b						
Total Gate Charge	Q _g	V _{DS} = 15 V, V _{GS} = 5 V, I _D = 9 A		13	24	nC
Gate-Source Charge	Q _{gs}			4		
Gate-Drain Charge	Q _{gd}			5.7		
Gate Resistance	R _g		0.2		2.4	Ω
Turn-On Delay Time	t _{d(on)}	V _{DD} = 15 V, R _L = 15 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _g = 6 Ω		16	25	ns
Rise Time	t _r			10	20	
Turn-Off Delay Time	t _{d(off)}			35	50	
Fall Time	t _f			13	20	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 1.0 A, di/dt = 100 A/μs		35	70	

Notes






- a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.



TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)




TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)





TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI4812DY-T1](#) [SI4812DY-T1-E3](#) [SI4812DY-E3](#) [SI4812DY](#)