

PRODUCT NUMBER

20020012-XXXXXXLF

20020012-

PITCH

C: 3.50mm
D: 3.81mm
G: 5.00mm
H: 5.08mm

POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

SCREW CODE

CODE	SCREW TYPE	AVAILABILITY
A	-/+	ON REQUEST ONLY
B	-	STANDARD

ALL FLANGE SCREWS ARE ONLY AVAILABLE IN +/-
COMBINATION SCREW TYPES.

PROPERTY TABLE

FCI SERIES NAME		03-350	03-381	03-500	03-508		
PITCH (mm)		3.50	3.81	5.00	5.08		
VOLTAGE RATING (VAC)		300	300	300	300		
CURRENT RATING (A)		10	10	10	10		
APPLICABLE WIRE RANGE (AWG)		1-WIRE	16~28	16~28	12~22	12~22	
		2-WIRE	20	20	18	18	
WIRE CROSS SECTION (mm ²)		SOLID	1-WIRE	1.5	1.5	2.5	2.5
			2-WIRE	0.5	0.5	1.0	1.0
		STRANDED	1-WIRE	1.5	1.5	2.5	2.5
			2-WIRE	0.75	0.75	1.5	1.5
OPENING CONTACT HOUSING(mm ²)		1.8x2.4	1.8x2.4	2.6x2.8	2.6x2.8		
WIRE STRIP LENGTH(mm)		6~7	6~7	6~7	6~7		
TORQUE +/– 10% (N-m/Lb-in)		0.19/1.7	0.19/1.7	0.4/3.5	0.4/3.5		
SCREW		M2x0.4	M2x0.4	M2.5x0.4	M2.5x0.4		
WITHSTANDING VOLTAGE (kV)		1.6	1.6	1.6	1.6		
OPERATING TEMP. (°C)		–40~+115	–40~+115	–40~+115	–40~+115		
POLES AVAILABLE		02~24	02~24	02~24	02~24		

SAFETY CERTIFICATE



NOTES:

1. MATERIALS

- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
1-2 SCREW: STEEL, ZINC PLATED.
1-3 CLAMP: COPPER ALLOY, NICKEL PLATED.
1-4 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCT SPECIFICATION REFER TO FCI GS-12-625.

3. PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.


4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN
ON PRODUCT SURFACE.5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE
EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family
				tolerances unless otherwise specified			TERMINAL BLOCK
ltr	ecn no	dr	date	angles	to line	MM [INCH]	title
A	T10-0082	WL	080810		X.±0.5		TERMINAL BLOCK
B	T10-0158	WL	100410		X.X±0.3		PLUGGABLE, PLUG, SIGNAL, W/FLANGE
C	T10-0180	WL	111510	X'±1°	X.XX±0.1	scale	FRONT SCREW
D	T10-0186	WL	120810	dr	WENDY CHEN	051810	sheet 1 of 5 size
E	T11-0006	WL	012611	enr	JASON HSU	051810	20020012 A4
F	T-005908	WL	091311	chr	GARY HSIEH	051810	type
				appd	JOSEPH HSIA	051810	CUSTOMER Drawing
sheet index	revision sheet	F	F	F	F	F	
		1	2	3	4	5	

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-CXXXXXL	03-350	3.50 mm




N = Number of poles

Dim A = $N \times 3.5 [0.138] + 0.80 [0.031]$ Dim B = $(N-1) \times 3.5 [0.138]$ Dim C = $(N-1) \times 3.5 [0.138] + 8.6 [0.339]$

Poles	Dim A	Dim B	Dim C
2-4p	$\pm 0.10 [0.004]$	$\pm 0.15 [0.006]$	
5-7p	$\pm 0.15 [0.006]$	$\pm 0.20 [0.008]$	
8-12p	$\pm 0.20 [0.008]$	$\pm 0.25 [0.010]$	
13-18p	$\pm 0.25 [0.010]$	$\pm 0.30 [0.012]$	
19-24p	$\pm 0.30 [0.012]$	$\pm 0.40 [0.016]$	




mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
F				TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW
				sheet 2 of 5 size
				20020012 A4
				type CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-DXXXXXLf	03-381	3.81 mm




N = Number of poles
 Dim A = $N \times 3.81 [.150] + 0.80 [.031]$
 Dim B = $(N-1) \times 3.81 [.150]$
 Dim C = $N \times 3.81 [.150] + 9.6 [.378]$
 Dim D = $(N-1) \times 3.81 [.150] + 9.0 [.354]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-11p	$\pm 0.20 [.008]$
12-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$






mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/FLANGE FRONT SCREW
F				dwg no 20020012
				sheet 3 of 5
				size A4
				type CUSTOMER Drawing
sheet index	revision sheet			

PRODUCT NUMBER	SERIES NAME	PITCH
20020012-GXXXXXL	03-500	5.00 mm






N = Number of poles
 Dim A = $N \times 5.0 [.197] + 0.5 [.020]$
 Dim B = $(N-1) \times 5.0 [.197]$
 Dim C = $N \times 5.0 [.197]$
 Dim D = $(N+1) \times 5.0 [.197]$
 Dim E = $(N+2) \times 5.0 [.197]$

Poles	Tolerance
2-7p	$\pm 0.15 [.006]$
8-12p	$\pm 0.25 [.010]$
13-18p	$\pm 0.30 [.012]$
19-24p	$\pm 0.40 [.016]$



mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5		TERMINAL BLOCK
				linear	X.X±0.3		PLUGGABLE, PLUG, SIGNAL, W/FLANGE
				X*±1*	X.XX±0.1	scale	FRONT SCREW
		dr	WENDY CHEN	051810		FCI	sheet 4 of 5 size
		enr	JASON HSU	051810			20020012
		chr	GARY HSIEH	051810			A4
		appd	JOSEPH HSIA	051810			type
sheet index	revision sheet						CUSTOMER Drawing


PRODUCT NUMBER	SERIES NAME	PITCH
20020012-HXXXXXXLF	03-508	5.08 mm



SECTION P-P

N = Number of poles
 Dim A = $N \times 5.08 [.200] + 0.50 [.020]$
 Dim B = $(N-1) \times 5.08 [.200]$
 Dim C = $N \times 5.08 [.200]$
 Dim D = $(N+1) \times 5.08 [.200]$
 Dim E = $(N+2) \times 5.08 [.200]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.25 [.010]$
13-18p	$\pm 0.30 [.012]$
19-24p	$\pm 0.40 [.016]$



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
F				angles	X.±0.5		TERMINAL BLOCK
				linear	X.X±0.3		PLUGGABLE, PLUG, SIGNAL, W/FLANGE
				X'±1"	X.XX±0.1	scale	FRONT SCREW
		dr	WENDY CHEN	051810			sheet 5 of 5 size
		enr	JASON HSU	051810			
		chr	GARY HSIEH	051810			
		appd	JOSEPH HSIA	051810			
sheet index	revision sheet						type CUSTOMER Drawing