

(0,50 mm) .0197" (HQCD) (0,80 mm) .0315" (EQCD)

EQCD-040-04.00-TTL-STR-2

Q STRIP® COAX CABLE ASSEMBLIES

SPECIFICATIONS

For complete specifications see
www.samtec.com?HQCD or
www.samtec.com?EQCD

Cable:
 38 AWG micro ribbon coax cable
Signal Routing:
 50Ω Single-Ended
Overall Length:
 (95,3 mm) 03.75" to
 (1 m) 40" standard
Cable Flexing Life:
 >10,000 cycles
Cable Bending Radius: <2,5mm
Plating:
 Au over 50μ" (1,27 μm) Ni
Current Rating:
 EQCD: 500 mA per pin
 HQCD: 300 mA per pin
 (6 adjacent pins powered)
Cable Propagation Delay:
 4.79 nsec/meter
Operating Temp Range:
 -25°C to +105°C
Unmating Force (-RT1 option):
 -RT1 option increases
 unmating force up to 50%
RoHS Compliant: Yes

HQCD Mates with:
 QTH, QSH


EQCD Mates with:
 QTE, QSE



0,50 mm or
 0,80 mm pitch

Socket or
 Terminal

Surface Mount
 or Panel Mount



38 AWG
 micro ribbon
 coax cable

Cable Length	Rated @ 7dB Insertion Loss	
	EQCD	HQCD
10" (0,25 m)	5.50 GHz / 11.00 Gbps	6.50 GHz / 13.00 Gbps

Performance and complete test data available at
www.samtec.com?EQCD, www.samtec.com?HQCD
 or contact sig@samtec.com

RECOGNITIONS

For complete scope
 of recognitions see
www.samtec.com/quality



APPLICATIONS



Processing conditions will
 affect mated height.

ALSO AVAILABLE (MOV Required)

- Other sizes and lengths
 - Other terminations
 - Other wire AWG
 - Retention pin
- Contact Samtec.

Note: Cable lengths longer
 than 40.00" (1 meter) are not
 supported with S.I. test data.

Note: Design your High Speed
 Cable with Samtec's High
 Speed Cable Solutionator® at
www.samtec.com/hdr

Note: This Series is
 non-standard, non-returnable.

TYPE

HQCD

= (0,50 mm) .0197" pitch

EQCD

= (0,80 mm) .0315" pitch


NO. OF POSITIONS PER ROW

–030, –060, –090
 (HQCD Series)


–020, –040, –060
 (EQCD Series)

WIRE LENGTH


–“XX.XX”
 = Wire Length in Inches
 (43,7 mm) 01.72" minimum





EQCD-020-40.00-TPU-TTR-1



HQCD-030-06.00-STL-TTR-1-B

**HQCD, EQCD SERIES**#4-40
ThreadPanel Mount
options**SCREW MOUNT
APPLICATIONS
(-F, -S, -B)**

SO-0318-04-01-02

Screw Down
options**END
NO. 1****END
NO. 2****WIRING OPTION****END OPTIONS**Specify
END ASSEMBLIES
from chart**PANEL MOUNT
END OPTION
APPLICATIONS
(-TPU, -TPD, -SPU, SPD)**

END 1 ONLY	PANEL MOUNT	
TPU		Terminal, Panel Mount, Notch Up
TPD		Terminal, Panel Mount, Notch Down
SPU		Socket, Panel Mount, Notch Up
SPD		Socket, Panel Mount, Notch Down

- 1**
= Pin 1 to Pin 1
- 2**
= Pin 1 to Pin 2
- 3**
= Pin 1 to Second to Last Pin
- 4**
= Pin 1 to Last Pin

END 1 or END 2	SURFACE MOUNT	
TTR		Terminal, Top Mount, Notch Right
TTL		Terminal, Top Mount, Notch Left
TBR		Terminal, Bottom Mount, Notch Right
TBL		Terminal, Bottom Mount, Notch Left
STR		Socket, Top Mount, Notch Right
STL		Socket, Top Mount, Notch Left
SBR		Socket, Bottom Mount, Notch Right
SBL		Socket, Bottom Mount, Notch Left

Leave blank for no Screw Mount
& Retention End Option**-F**
= Screw Mount End No. 1 only
(N/A with XPX options)**-S**
= Screw Mount End No. 2 only**-B**
= Screw Mount Both Ends
(N/A with XPX options)**-1**
= End No. 1 Screw Mount.
End No. 2 Retention Pin or Socket**-2**
= End No. 1 Retention Pin or Socket.
End No. 2 Screw Mount Option