

SiC

Silicon Carbide Diode

5th Generation thinQ!™

650V SiC Schottky Diode

IDW40G65C5

Final Datasheet

Rev. 2.2, 2013-01-15

Power Management & Multimarket

5th Generation thinQ!™ SiC Schottky Diode

IDW40G65C5

1 Description

ThinQ!™ Generation 5 represents Infineon leading edge technology for the SiC Schottky Barrier diodes. Thanks to the more compact design and thin-wafer technology, the new family of products shows improved efficiency over all load conditions, resulting from both the improved thermal characteristics and a lower figure of merit ($Q_c \times V_f$).

The new thinQ!™ Generation 5 has been designed to complement our 650V CoolMOS™ families: this ensures meeting the most stringent application requirements in this voltage range.

Features

- Revolutionary semiconductor material - Silicon Carbide
- Benchmark switching behavior
- No reverse recovery/ No forward recovery
- Temperature independent switching behavior
- High surge current capability
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC¹⁾ for target applications
- Breakdown voltage tested at 88 mA²⁾
- Optimized for high temperature operation

Benefits

- System efficiency improvement over Si diodes
- System cost / size savings due to reduced cooling requirements
- Enabling higher frequency / increased power density solutions
- Higher system reliability due to lower operating temperatures
- Reduced EMI

Applications

- Switch mode power supply
- Power factor correction
- Solar inverter
- Uninterruptible power supply





Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DC}	650	V
$Q_C; V_R=400V$	55	nC
$E_C; V_R=400V$	12.8	μJ
$I_F @ T_C < 110^\circ C$	40	A

Table 2 Pin Definition

Pin 1	Pin 2	Pin 3
n.c.	C	A

Type / ordering Code	Package	Marking	Related links
IDW40G65C5	PG-TO247-3	D4065C5	www.infineon.com/sic

1) J-STD20 and JESD22

2) All devices tested under avalanche conditions for a time periode of 10ms

Table of Contents

1	Description.....	2
2	Maximum ratings.....	4
3	Thermal characteristics.....	4
4	Electrical characteristics.....	5
5	Electrical characteristics diagrams.....	6
6	Simplified Forward Characteristics Model	8
7	Package outlines.....	9
8	Revision History	10

2 Maximum ratings

Table 3 Maximum ratings

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Continuous forward current	I_F	—	—	40	A	$T_C < 110^\circ\text{C}$, $D=1$
Surge non-repetitive forward current, sine halfwave	$I_{F,SM}$	—	—	182		$T_C = 25^\circ\text{C}$, $t_p=10\text{ ms}$
		—	—	153		$T_C = 150^\circ\text{C}$, $t_p=10\text{ ms}$
Non-repetitive peak forward current	$I_{F,max}$	—	—	1432		$T_C = 25^\circ\text{C}$, $t_p=10\text{ }\mu\text{s}$
i^2t value	$\int i^2 dt$	—	—	166	A ² s	$T_C = 25^\circ\text{C}$, $t_p=10\text{ ms}$
		—	—	118		$T_C = 150^\circ\text{C}$, $t_p=10\text{ ms}$
Repetitive peak reverse voltage	V_{RRM}	—	—	650	V	
Diode dv/dt ruggedness	dv/dt	—	—	100	V/ns	$V_R=0..480\text{ V}$
Power dissipation	P_{tot}	—	—	183	W	$T_C = 25^\circ\text{C}$
Operating and storage temperature	$T_j; T_{stg}$	-55	—	175	°C	
Mounting torque		—	50	70	Ncm	M3 and M4 screws

3 Thermal characteristics

Table 4 Thermal characteristics TO-247-3

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction-case	R_{thJC}	—	0.6	0.8	K/W	
Thermal resistance, junction-ambient	R_{thJA}	—	—	62		leaded
Soldering temperature, wavesoldering only allowed at leads	T_{sold}	—	—	260	°C	1.6mm (0.063 in.) from case for 10 s

4 Electrical characteristics

Table 5 Static characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
DC blocking voltage	V_{DC}	650	–	–	V	$I_R = 0.22 \text{ mA}$, $T_j = 25^\circ\text{C}$
Diode forward voltage	V_F	–	1.5	1.7		$I_F = 40 \text{ A}$, $T_j = 25^\circ\text{C}$
		–	1.8	2.1		$I_F = 40 \text{ A}$, $T_j = 150^\circ\text{C}$
Reverse current	I_R	–	2.2	220	μA	$V_R = 650 \text{ V}$, $T_j = 25^\circ\text{C}$
		–	0.5	150		$V_R = 600 \text{ V}$, $T_j = 25^\circ\text{C}$
		–	8.2	1500		$V_R = 650 \text{ V}$, $T_j = 150^\circ\text{C}$

Table 6 AC characteristics

Parameter	Symbol	Values			Unit	Note/Test Condition
		Min.	Typ.	Max.		
Total capacitive charge	Q_c	–	55		nC	$V_R = 400 \text{ V}$, $di/dt = 200 \text{ A}/\mu\text{s}$, $I_F \leq I_{F,MAX}$, $T_j = 150^\circ\text{C}$.
Total Capacitance	C	–	1140	–	pF	$V_R = 1 \text{ V}$, $f = 1 \text{ MHz}$
		–	147	–		$V_R = 300 \text{ V}$, $f = 1 \text{ MHz}$
		–	145	–		$V_R = 600 \text{ V}$, $f = 1 \text{ MHz}$

5 Electrical characteristics diagrams

Table 7



Power dissipation	Diode forward current
	
$P_{\text{tot}} = f(T_c); R_{\text{thJC,max}}$	$I_F = f(T_c); T_j \leq 175^\circ\text{C}; R_{\text{thJC,max}}; \text{parameter } D = \text{duty cycle}$

Table 8





Typical forward characteristics	Typical forward characteristics in surge current
	
$I_F = f(V_F); t_p = 200 \mu\text{s}; \text{parameter: } T_j$	$I_F = f(V_F); t_p = 200 \mu\text{s}; \text{parameter: } T_j$

Table 9

Typ. capacitance charge vs. current slope ¹⁾	Typ. reverse current vs. reverse voltage
	
$Q_C = f(dI_F/dt)$; $T_J = 150^\circ\text{C}$; $V_R = 400\text{ V}$; $I_F \leq I_{F,\text{max}}$	$I_R = f(V_R)$; parameter: T_J

1) Only capacitive charge, guaranteed by design.

Table 10





Max. transient thermal impedance	Typ. capacitance vs. reverse voltage
	
$Z_{th,jc} = f(t_p)$; parameter: $D = t_p / T$	$C = f(V_R)$; $T_J = 25^\circ\text{C}$; $f = 1\text{ MHz}$

Table 11

Typ. capacitance stored energy
 $E_C = f(V_R)$

6 Simplified Forward Characteristics Model

Table 12

Equivalent forward current curve	Mathematical Equation
 $V_F = f(I_F)$	$V_F = V_{TH} + R_{DIFF} \cdot I_F$ $V_{TH}(T_j) = -0.001 \cdot T_j + 1.04 \text{ [V]}$ $R_{DIFF}(T_j) = 3.2 \cdot 10^{-7} \cdot T_j^2 + 3.2 \cdot 10^{-5} \cdot T_j + 0.012 \text{ [}\Omega\text{]}$
	T_j in °C; $-55^\circ\text{C} < T_j < 175^\circ\text{C}$; $I_F < 80 \text{ A}$

7 Package outlines




Figure 1 Outlines TO-247, dimensions in mm/inches

8 Revision History

5th Generation thinQ!™ SiC Schottky Diode

Revision History: 2013-01-15, Rev. 2.2

Previous Revision:

Revision	Subjects (major changes since last version)
2.0	Release of the final datasheet.
2.1	Reverse current values, maximum diode forward voltage.
2.2	Reverse current values, tested avalanche current, simplified calculation model

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?

Your feedback will help us to continuously improve the quality of this document.

Please send your proposal (including a reference to this document) to: erratum@infineon.com

Edition 2013-01-15

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2013 Infineon Technologies AG

All Rights Reserved.



Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

www.infineon.com