

Technical drawings of the PANDUIT connector. The left side shows two side views: the top one is a perspective view of the connector with dimensions E, D, $B \pm .010 (.25)$, F REF., and $A \pm .010 (.25)$; the bottom one is a cross-sectional view showing the internal structure with dimension C. The right side shows three views: a top view of the connector with dimensions 19.0 (482.6) and G, and a side view of the connector with dimension H. A dashed circle indicates the location of "DETAIL A" on the side view.

PANDUIT PART NO.*	BUNDLE DIA.		A	B	C	D	E	F	G	H	MINIMUM LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs. (g) /100 pcs
	MIN IN. (mm)	MAX IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)	IN. (mm)				
PLT2S-VMR	.06 (1.5)	1.94 (49.3)	.047 (1.2)	.190 (4.8)	.258 (6.6)	.220 (5.6)	.316 (8.0)	8.1 (206)	8.5 (216)	9.3 (236)	50 (222)	STANDARD	.32 (147)
PLT3S-VMR		2.75 (69.9)							11.3 (287)	11.8 (298)			12.5 (318)

*1) SEE www.panduit.com FOR PART MATERIAL & COLOR SUFFIX DESIGNATIONS.
2) STANDARD PACKAGING: 2500 STRAPS PER REEL; 2 REELS PER CARTON (2S), 1 REEL PER CARTON (3S)
3) PACKAGED FOR USE WITH PAT2S AND PAT3S TOOLS AND DISPENSERS.
4) LISTED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

										CAD FILENAME/LAYERS		W10030BY/02 SS-26588				
										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS						
										PANDUIT CORP. TINLEY PARK, ILLINOIS VMR PAN-TY CABLE TIES PACKAGED FOR AUTOMATIC TOOLS UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.10(2.5) (.XXX) ±.020(.51) (.XX) ±.02(.5) ANGLES ± -----						
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.						
										DRAWN BY	MAT'L:		SCALE		NONE	
										RAM	NYLON 6.6					
										DATE			DRAWING NO.		DWG	
										4/8/92			SS-26588		A	
										CHK'D			SIZE			
										HVP						
2	11/6/08	TRAM		NEW ROW ADDED FOR PLT3S, CHANGED 2S MAX BUNDLE			25688	2								
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP						