

FDC6310P

Dual P-Channel 2.5V Specified PowerTrench[®] MOSFET

General Description

These P-Channel 2.5V specified MOSFETs are produced using Fairchild Semiconductor's advanced PowerTrench process that has been especially tailored to minimize on-state resistance and yet maintain low gate charge for superior switching performance.



These devices have been designed to offer exceptional power dissipation in a very small footprint for applications where the bigger more expensive SO-8 and TSSOP-8 packages are impractical.

Applications

- Load switch
- Battery protection
- Power management

Features

- -2.2 A, -20 V. $R_{DS(ON)} = 125 \text{ m}\Omega$ @ $V_{GS} = -4.5 \text{ V}$
 $R_{DS(ON)} = 190 \text{ m}\Omega$ @ $V_{GS} = -2.5 \text{ V}$
- Low gate charge
- Fast switching speed
- High performance trench technology for extremely low $R_{DS(ON)}$
- SuperSOTTM -6 package: small footprint 72% smaller than standard SO-8; low profile (1mm thick)



Absolute Maximum Ratings

$T_A=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Ratings	Units
V_{DSS}	Drain-Source Voltage	-20	V
V_{GSS}	Gate-Source Voltage	± 12	V
I_D	Drain Current – Continuous	-2.2	A
	– Pulsed		
P_D	Power Dissipation for Single Operation	0.96	W
		0.9	
		0.7	
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	$^\circ\text{C}$

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	130	$^\circ\text{C}/\text{W}$
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	60	$^\circ\text{C}/\text{W}$

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
.310	FDC6310P	7"	8mm	3000 units


Electrical Characteristics

$T_A = 25^\circ\text{C}$ unless otherwise noted


Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{\text{GS}} = 0 \text{ V}$, $I_D = -250 \mu\text{A}$	-20			V
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = -250 \mu\text{A}$, Referenced to 25°C		-11		mV°C
$I_{\text{DS}}^{\text{SS}}$	Zero Gate Voltage Drain Current	$V_{\text{DS}} = -16 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$			-1	μA
I_{GSSF}	Gate-Body Leakage, Forward	$V_{\text{GS}} = 12 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$			100	nA
I_{GSSR}	Gate-Body Leakage, Reverse	$V_{\text{GS}} = -12 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$			-100	nA
On Characteristics (Note 2)						
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{DS}} = V_{\text{GS}}$, $I_D = -250 \mu\text{A}$	-0.6	-1.0	-1.5	V
$\frac{\Delta V_{\text{GS(th)}}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	$I_D = -250 \mu\text{A}$, Referenced to 25°C		3		mV°C
$R_{\text{DS(on)}}$	Static Drain-Source On-Resistance	$V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -2.2 \text{ A}$ $V_{\text{GS}} = -2.5 \text{ V}$, $I_D = -1.8 \text{ A}$ $V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -2.2 \text{ A}$, $T_J = 125^\circ\text{C}$	100 145 137	125 190 184		$\text{m}\Omega$
$I_{\text{D(on)}}$	On-State Drain Current	$V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DS}} = -5 \text{ V}$	-6			A
g_{FS}	Forward Transconductance	$V_{\text{DS}} = -5 \text{ V}$, $I_D = -3.5 \text{ A}$		6		S
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{\text{DS}} = -10 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$, $f = 1.0 \text{ MHz}$		337		pF
C_{oss}	Output Capacitance			88		pF
C_{rss}	Reverse Transfer Capacitance			51		pF
Switching Characteristics (Note 2)						
$t_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}} = -10 \text{ V}$, $I_D = -1 \text{ A}$, $V_{\text{GS}} = -4.5 \text{ V}$, $R_{\text{GEN}} = 6 \Omega$		9	18	ns
t_r	Turn-On Rise Time			12	22	ns
$t_{\text{d(off)}}$	Turn-Off Delay Time			10	20	ns
t_f	Turn-Off Fall Time			5	10	ns
Q_g	Total Gate Charge	$V_{\text{DS}} = -10 \text{ V}$, $I_D = -2.2 \text{ A}$, $V_{\text{GS}} = -4.5 \text{ V}$		3.7	5.2	nC
Q_{gs}	Gate-Source Charge			0.65		nC
Q_{gd}	Gate-Drain Charge			1.3		nC
Drain-Source Diode Characteristics and Maximum Ratings						
I_{S}	Maximum Continuous Drain-Source Diode Forward Current				-0.8	A
V_{SD}	Drain-Source Diode Forward Voltage	$V_{\text{GS}} = 0 \text{ V}$, $I_{\text{S}} = -0.8 \text{ A}$ (Note 2)		0.77	-1.2	V

Notes:


- R_{thJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{thJC} is guaranteed by design while R_{thCA} is determined by the user's board design.



a) 130°C/W when mounted on a 0.125 in^2 pad of 2 oz. copper.



b) 140°C/W when mounted on a 0.004 in^2 pad of 2 oz copper



c) 180°C/W when mounted on a minimum pad.

Scale 1 : 1 on letter size paper

- Pulse Test: Pulse Width $< 300\mu\text{s}$, Duty Cycle $< 2.0\%$

Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics




Figure 7. Gate Charge Characteristics.




Figure 8. Capacitance Characteristics.




Figure 9. Maximum Safe Operating Area.




Figure 10. Single Pulse Maximum Power Dissipation.




Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1c.
Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE TM	FAST [®]	OPTOPLANAR [™]	SuperSOT [™] -3
Bottomless [™]	FASTR [™]	PACMAN [™]	SuperSOT [™] -6
CoolFET [™]	FRFET [™]	POP [™]	SuperSOT [™] -8
CROSSVOLT [™]	GlobalOptoisolator [™]	PowerTrench [®]	SyncFET [™]
DenseTrench [™]	GTO [™]	QFET [™]	TinyLogic [™]
DOME [™]	HiSeC [™]	QS [™]	UHC [™]
EcoSPARK [™]	ISOPLANAR [™]	QT Optoelectronics [™]	UltraFET [®]
E ² CMOS [™]	LittleFET [™]	Quiet Series [™]	VCX [™]
EnSigna [™]	MicroFET [™]	SILENT SWITCHER [®]	
FACT [™]	MICROWIRE [™]	SMART START [™]	
FACT Quiet Series [™]	OPTOLOGIC [™]	Stealth [™]	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.