





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE



LOCK WASHER



HEX NUT

NOTE:

1. SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.
2. MOUNTING TORQUE NOT TO EXCEED 3 lb-in.

MIN. CAP (pF)	WORKING VOLTAGE	CURRENT	DWV (VDC)	I.R. MIN. @ 100 (VDC.)	MINIMUM NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220		
	125°C				100 MHz	1 GHz	10 GHz
1000	100	10A	250	10 G Ω	65	70	70

X-2015 Rev-0	REVISION RECORD		Original Release C.O. 20021003-3-01 100MHz WAS 45, 1GHz WAS 60 & 10GHz WAS 60. S.M. 01-13-04 20040113-1-01		--TOLERANCES-- Unless Otherwise Specified		Title MIL-15733/61-0008 BUSHING STYLE EMI FILTER		
	0				DECIMAL ± .031 [0.79]				
	1				ANGLES ± 		Drawn L.E. 10-03-02		Scale 4 X
					TUSONIX TUCSON, ARIZONA		Approved T.C. 10-03-02		
							A	4201-502	