







Amp	Volt	Hz	IP Ident. colour + h	Part No.	Wall socket outlets 2 P +  IEC/EN 60 309	  9	EAN-No 4015609...																																	
 IP44					mondo small version , flush-type, RAL 1013 pearl white with flush-type socket outlet, with plaster thickness adjustment    <table><tr><th>Ampère</th><th>d</th><th>e</th><th>f</th><th>r</th></tr><tr><td>16 A</td><td>80</td><td>70</td><td>33</td><td>96</td></tr></table>	Ampère	d	e	f	r	16 A	80	70	33	96	10 155	019342 019335 019366 173631 173648																							
Ampère	d	e	f	r																																				
16 A	80	70	33	96																																				
16	230	50/60	6	418 306																																				
	110	50/60	4	418 304																																				
	400	50/60	9	418 309																																				
230 50/60 6 418 306RW RW = clear white, RAL 9010																																								
230 50/60 6 418 306LG LG = light grey, RAL 7035																																								
 IP67					internal fixing means, 2 cable entries both, top and bottom (knock-out)    <table><tr><th>Ampère</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>l</th><th>n</th><th>u</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>140</td><td>47,5</td><td>164</td><td>72</td><td>7</td><td>16/21</td></tr><tr><td>32 A</td><td>66,5</td><td>5</td><td>96</td><td>95</td><td>154</td><td>47,5</td><td>176</td><td>96</td><td>7</td><td>16/21</td></tr></table>	Ampère	b	c	d	e	f	l	n	u	v	Pg	16 A	66,5	5	96	95	140	47,5	164	72	7	16/21	32 A	66,5	5	96	95	154	47,5	176	96	7	16/21	5 409	010165 010158 010172
Ampère	b	c	d	e		f	l	n	u	v	Pg																													
16 A	66,5	5	96	95		140	47,5	164	72	7	16/21																													
32 A	66,5	5	96	95		154	47,5	176	96	7	16/21																													
16	230	50/60	6	119 306																																				
	110	50/60	4	119 304																																				
	400	50/60	9	119 309																																				
cable gland Pg 16 enclosed																																								
32	230	50/60	6	139 306																																				
	110	50/60	4	139 304																																				
	400	50/60	9	139 309																																				
cable gland Pg 21 enclosed																																								
 IP67					internal fixing means, cable entries: 1 x top open, 2 x bottom (knock-out) and vice versa    <table><tr><th>Ampère</th><th>a</th><th>b</th><th>c</th><th>d</th><th>e</th><th>f</th><th>n</th><th>u</th><th>v</th><th>Pg</th></tr><tr><td>16 A</td><td>134,5</td><td>103</td><td>6</td><td>170</td><td>118</td><td>171</td><td>216</td><td>114</td><td>/</td><td>29</td></tr></table>	Ampère	a	b	c	d	e	f	n	u	v	Pg	16 A	134,5	103	6	170	118	171	216	114	/	29	2 865	125715 173655 149360											
Ampère	a	b	c	d		e	f	n	u	v	Pg																													
16 A	134,5	103	6	170		118	171	216	114	/	29																													
63	230	50/60	6	169 306																																				
	110	50/60	4	169 304																																				
	400	50/60	9	169 309																																				