

July 2016

Chip beads

For power line

MPZ series (for automobiles)

MPZ2012 Type

MPZ2012 2012[0805 inch]*

* Dimensions code JIS[EIA]

Reminders for using these products

Before using these products, be sure to request the delivery specifications.

Safety reminders

Please pay sufficient attention to the warnings for safe designing when using this products.

<u> </u>
The storage period is less than 12 months.Be sure to follow the storage conditions (temperature:5 to 40°C, humidity:10 to 75% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
On not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
 Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
 Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
On not expose the products to magnets or magnetic fields.
On not use for a purpose outside of the contents regulated in the delivery specifications.
The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition. The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society,
person or property.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (electric trains, ships, etc.)

set forth in the each catalog, please contact us.

- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions



Chip beads

For power line

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders
AEC-Q200

Overview of MPZ2012 type


FEATURES

- O Noise reduction solution for power line.
- Ocompared to the MMZ series, has low direct current resistance for compatibility with large currents, optimal for low power consumption.
- O Performs well even in signal lines where low direct current resistance is required.

APPLICATION

Various ECUs, powertrains, body controls, and car multimedia (telematics).

PART NUMBER CONSTRUCTION



OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

	Temperati	ure ranges	Package quantity	Individual weight
Туре	Operating temperature	Storage temperature*		
	(°C)	(°C)	(pieces/reel)	(mg)
MPZ2012	-55 to +125	-55 to +125	4.000	8


^{*} The storage temperature range is for after the circuit board is mounted.

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

O Halogen-free: indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.



■ RECOMMENDED REFLOW PROFILE




Preheatir	ng		Soldering		Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3
150°C	180°C	60 to 120s	230°C	30 to 60s	250 to 260°C	10s



■ MATERIAL CHARACTERISTIC


S material: Standard type that features impedance characteristics similar to those of a typical ferrite core. For signal line applications in which the blocking region is near 100MHz. Impedance values selected for effectiveness at 40 to 300MHz.

TYPICAL MATERIAL IMPEDANCE CHARACTERISTICS






■SHAPE & DIMENSIONS





Dimensions in mm

■ RECOMMENDED LAND PATTERN



Dimensions in mm



ELECTRICAL CHARACTERISTICS

CHARACTERISTICS SPECIFICATION TABLE

Impedance		DC resistance	Rated current*	Part No.
[100MHz]				
(Ω)	Tolerance	(Ω)max.	(A)max.	
30	±10Ω	0.010	6	MPZ2012S300ATD25
100	±25%	0.020	4	MPZ2012S101ATD25
220	±25%	0.040	3	MPZ2012S221ATD25
330	±25%	0.050	2.5	MPZ2012S331ATD25
600	±25%	0.100	2	MPZ2012S601ATD25
1000	±25%	0.150	1.5	MPZ2012S102ATD25


^{*} Please refer to the graph of rated current vs. temperature characteristics (derating) about the rating current at 85°C or more in temperature of the product.

O Measurement equipment

Measurement item	Product No.	Manufacturer
Impedance	E4991A+16192A	Keysight Technologies
DC resistance	Type-7556	Yokogawa

^{*} Equivalent measurement equipment may be used.

O Rated current vs. temperature characteristics (derating)






ELECTRICAL CHARACTERISTICS

□ Z VS. FREQUENCY CHARACTERISTICS (BY SERIES)

MPZ2012S series







ELECTRICAL CHARACTERISTICS

Z, X, R VS. FREQUENCY CHARACTERISTICS


MPZ2012S300ATD25




MPZ2012S101ATD25




MPZ2012S221ATD25




MPZ2012S331ATD25



MPZ2012S601ATD25




MPZ2012S102ATD25






■PACKAGING STYLE

□REEL DIMENSIONS




Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm

Туре	Α	В	P1	K
MPZ2012	1.5±0.2	2.3±0.2	4.0±0.1	1.1max.



Dimensions in mm