

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HBDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	CHANGE DATE CODE&TE LOGO ECO-08-007851	07-Apr-08	CY.Z	BH.Y
	C1	CHANGE LOGO& ADD LINE IDENTIFICATION ECO-12-001771	21Aug2012	YS.H	BH.Y



PART B

PART A

(C1)

(C)

TE

0JE-SH-112LMH

12V



8A 240V~

8A 250V~

OEG

MADE IN CHINA

SEE NOTE 5

LOT NO.

(C1)



0.45

0.3



0.3

14.6±0.5

4.1±0.3



CONNECTION FIGURE

FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H.SASAKI

CHK Y.OIKAWA

APVD S.NAGAI

PRODUCT SPEC

SEE PRODUCT SPEC

APPLICATION SPEC


—

WEIGHT —

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± —
1 PLC	± —
2 PLC	± —
3 PLC	± —
4 PLC	± —
ANGLES	± —

MATERIAL

FINISH



TE Connectivity

NAME

OJE-SH-LMH CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

1461403

RESTRICTED TO

A3

00779

C=

1461403

SCALE 5:1

SHEET 1 OF 2

REV C1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By - TE CONNECTIVITY		ALL RIGHTS RESERVED.	

LOC HB	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		—	—	SEE SHEET 1	—	—	—

ACTIVE	1461403-5	OJE-SH-124LMH	107-79010	24V	OJE-SH-124LMH	f
ACTIVE	1461403-4	OJE-SH-112LMH	107-79010	12V	OJE-SH-112LMH	e
ACTIVE	1461403-2	OJE-SH-109LMH	107-79010	9V	OJE-SH-109LMH	d
Ⓒ1 OBSOLETE	1461403-1	OJE-SH-106LMH	107-79010	6V	OJE-SH-106LMH	c
ACTIVE	1461403-3	OJE-SH-105LMH	107-79010	5V	OJE-SH-105LMH	b
Ⓒ1 OBSOLETE	1461403-6	OJE-SH-103LMH	107-79010	3V	OJE-SH-103LMH	a
PART STATUS	TE PART NO	TE TYPE NAME	PACKAGE SPEC	PART B	PART A	TYPE

RELAY TYPE

- Ⓒ Ⓑ

NOTES:
1.LOT NO. SYSTEM AS FOLLOWING:

0547

WEEK
YEAR
- Ⓒ1

2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;
- Ⓒ1

3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.
- Ⓒ

4.MARKING FROM INK TO LASER.
- Ⓒ1

5.ADD LOT NO. SYSTEM AS FOLLOWING;

11A

I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....
7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY
1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;
III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY,
SUCH AS: A,B,.....Z
- | | | | | |
|------------------|------------|-------------|----------------------|------|
| | | UV RESIN | SEEL (VENT HOLE) | 16 |
| | | EPOXY RESIN | SEEL (BASE & BOBBIN) | 15 |
| | | 3UEW | MAGNETIC WIRE | 14 |
| 94V-0 | | P.B.T | CASE | 13 |
| 94V-0 | | P.B.T | BASE | 12 |
| 94V-0 | | P.B.T | BOBBIN | 11 |
| | SOLDER DIP | C.P WIRE | COIL TERMINAL | 10 |
| 94V-0 | | P.P.S | CARD | 9 |
| | | Ag ALLOY | MOVABLE CONTACT | 8 |
| | | Ag ALLOY | NO.CONTACT | 7 |
| | | STEEL | HINGE SPRING | 6 |
| | SOLDER DIP | Cu ALLOY | NO.TERMINAL | 5 |
| | SOLDER DIP | Cu ALLOY | MOVABLE SPRING | 4 |
| | NIP | STEEL | CORE | 3 |
| | NIP | STEEL | ARMATURE | 2 |
| | NIP | STEEL | YOKE | 1 |
| INCOMBUSTIBILITY | TREATMENT | MATERIAL | DESCRIPTION | ITEM |
- | | | | | | | |
|--|-------------|------------------|-----------------------------|--------------------|--------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN
H,SASAKI | — | | | |
| | | CHK
Y.OIKAWA | — | | | |
| DIMENSIONS:
mm | | APVD
S.NAGAI | NAME | | | |
| | | PRODUCT SPEC | — | | | |
| | | SEE PRODUCT SPEC | OJE-SH-LMH CUSTOMER DRAWING | | | |
| | | APPLICATION SPEC | — | | | |
| MATERIAL
— | FINISH
— | WEIGHT
— | SIZE
A3 | CAGE CODE
00779 | DRAWING NO
C= 1461403 | RESTRICTED TO
— |
| CUSTOMER DRAWING | | | SCALE
5:1 | SHEET
2 OF 2 | REV
C1 | |
- 1470-19 (3/11)