

Low Phase Noise Clock Evaluation Module

Contents

1	Features	1
2	General Description	2
3	Signal Path and Control Circuitry	2
4	Getting Started	2
5	Input Clock Selection	2
6	Operating Mode Selection	3
7	Output Buffer Termination	5
8	Schematic	7

1 Features

- Easy-to-use evaluation module to generate low phase noise clocks
- Easy device setup
- Rapid configuration
- Control pins configurable through jumpers
- Requires 3.3-V power supply
- Single-ended or crystal input clock reference
- Termination available for LVPECL, LVDS, and LVCMOS output clocks




Figure 1. CDCM6100xEVM Evaluation Board

2 General Description

The CDCM61001, CDCM61002, and CDCM61004 are high-performance, low phase noise clock generators. Each device has one crystal/low-voltage CMOS (LVCMOS) input buffer and one, two, or four universal outputs depending on the respective device.

This is a programmable clock generator with control pins only. No EEPROM or programming interface is necessary to program these devices.

The CDCM6100x evaluation module (EVM) is designed to demonstrate the electrical performance of the CDCM61004 and is representative of the performance of the CDCM61001 and CDCM61002. This fully-assembled and factory-tested evaluation board allows complete validation of all device functions.

For optimum performance, the board is equipped with 50-Ω SMA connectors and well-controlled, 50-Ω impedance microstrip transmission lines.

Throughout this document, the abbreviation *EVM* and the phrases *evaluation module* and *evaluation board* are synonymous with the CDCM6100xEVM. For clarity of reading, the abbreviation *CDCM6100x* refers to the CDCM61001, CDCM61002, and CDCM61004, unless otherwise noted.

2.1 Reference Documents

The related documents listed in [Table 1](#) are available through the Texas Instruments web site at www.ti.com.

Table 1. EVM-Compatible Device Data Sheets

Device	Data Sheet
CDCM61001	SCAS869
CDCM61002	SCAS870
CDCM61004	SCAS871

3 Signal Path and Control Circuitry

The CDCM6100x supports either a crystal input or a single-ended clock with a frequency range of 21.875 MHz to 28.47 MHz. The internal VCO operates from 1.75 GHz to 2.05 GHz. The output buffers provide output frequencies from 43.75 MHz to 683.264 MHz for low-voltage differential signaling (LVDS) and low-voltage positive emitter coupled logic (LVPECL), and from 43.75 MHz to 250 MHz for LVCMOS. An optional, bypassed LVCMOS output is also available.

The output frequency depends on the input frequency, Prescaler, Feedback, and Output Divider settings. See the respective product data sheet (listed in [Table 1](#)) for complete descriptions of the various settings.

4 Getting Started

The EVM has self-explanatory labeling. Additionally, the naming conventions used for the EVM correspond to that used in the respective product data sheets. Words shown in ***bold italics*** in this document show the same name and label on the EVM board itself. The EVM can be used with either a crystal input or external, single-ended clock input.

4.1 Power-Supply Connection

Connect the power-supply source to the banana plug labeled ***3.3V (P4)*** and connect the ground of the power-supply source to ***GND (P5)***. There are decoupling capacitors and ferrite bead to isolate the device power pins dedicated for the PLL from the other power pins.


This EVM can operate from a 3.0-V to 3.6-V supply voltage.

5 Input Clock Selection

The CDCM6100xEVM offers the options to use either a crystal or a single-ended clock source as the clock input.

5.1 Configuring a Crystal Input

The EVM is available with an optional 25-MHz crystal. The EVM offers a dual footprint for a 6-pin (5 mm × 7 mm) and 4-pin (3 mm × 5 mm) crystal. For a parallel load resonant crystal, the configuration should be similar to that shown in [Figure 2](#).



Note: This configuration assumes that the crystal is placed very close to the XIN pin on the device.

Figure 2. CDCM6100xEVM Configuration with Parallel Load Resonant Crystal Clock Source

5.2 Configuring a Single-Ended Input

For a single-ended clock, remove the crystal if the board already has a crystal installed. Use SMA connector J101 for a single-ended input clock. Place a 50-Ω resistor in R69 if the clock is provided from a signal generator and if the signal generator requires a 50-Ω load for its operation. If the input clock is provided from another board or the LVCMOS buffer, do not place any resistor here.

Capacitor **C61** (100 nF) is required for ac coupling, as shown in [Figure 3](#).




Figure 3. Single-Ended Connection Configuration

6 Operating Mode Selection

The CDCM6100x is a PLL-based device and offers several modes of operation. Selection of the available control pins provides a set of output frequencies with different signaling levels. See the respective product data sheets for detailed device configuration information.

6.1 Prescaler Divider and Feedback Divider Settings

JP17 (PR1) and **JP18 (PR0)** are the control pin jumpers for Prescaler Divider and Feedback Divider selection, respectively. Use these jumpers only for logic '0'. These pins have internal 150-kΩ pull-up resistors; it is recommended to use the internal pull-up resistor only for logic '1'.

[Table 2](#) summarizes the available prescaler divider and feedback divider values with the corresponding PFD frequency range.

Table 2. Available Prescaler Divider and Feedback Divider Values with PFD Frequency Range

Control Inputs		Prescaler Divider	Feedback Divider	PFD Frequency ⁽¹⁾	
PR1	PR0			Minimum	Maximum
0	0	3	24	24.305	28.47
0	1	5	15	23.33	27.33
1	0	3	25	23.33	27.33
1	1	4	20	21.875	25.62

⁽¹⁾ PFD frequency = Reference Clock Frequency

The product of the prescaler divider and the feedback divider with reference clock frequency provides the frequency at which the VCO operates:

$$\text{VCO Frequency} = \text{Prescaler Divider} \times \text{Feedback Divider} \times \text{Reference Clock Frequency}$$

6.2 Output Divider Selections

JP14 (OD0), **JP13 (OD1)**, and **JP12 (OD2)** are the jumpers for the output dividers. Depending on whether the device operates in logic '1' or logic '0', the divider offers up to six different frequencies. All outputs have the same frequency because the outputs are generated from the same divider.

Table 3 lists the available output divider values.

Table 3. Programmable Output Divider Values

Control Inputs			Output Divider
OD2	OD1	OD0	
0	0	0	1
0	0	1	2
0	1	0	3
0	1	1	4
1	0	1	6
1	1	1	8

$$\text{Output Frequency} = \text{VCO Frequency} / (\text{Prescaler Divider} \times \text{Output Divider})$$

6.3 Output Buffer Type Selection

JP16 (OS1) and **JP15 (OS0)** are the jumpers for output buffer selection (LVCMOS, LVDS, or LVPECL). Each output pair provides two in-phase LVCMOS clocks.

Table 4 shows the output buffer options.

Table 4. Output Buffer Options

Control Inputs		Output Type
OS1	OS0	
0	0	LVCMOS, OSC_OUT Off
0	1	LVDS, OSC_OUT Off
1	0	LVPECL, OSC_OUT Off
1	1	LVPECL, OSC_OUT On

NOTE: A bypassed output (same as the reference clock frequency) is only available with LVPECL outputs.

6.4 Using ENABLE and $\overline{\text{RSTN}}$ Pins

JP22 (CHIP-DISABLE) is the jumper for the CE pin. This pin has an internal, 150-k Ω , pull-up resistor; it is recommended to use the internal pull-up resistor only for logic '1'.

Table 5 summarizes the power-down configuration.

Table 5. Power-Down Configuration

Control Input	Operating Condition	Output
CE		
0	Power Down	Hi-Z
1	Normal	Active

Do not connect this jumper for normal operation.

The $\overline{\text{RSTN}}$ pin is connected to both **CHIP_RESET** jumper **JP21** and pushbutton switch **RESET1**. Either option can be used to reset the device (including recalibrating the PLL). If any settings change on either the **PR0** or the **PR1** pins, PLL recalibration is required to generate the proper VCO frequency.

Table 6 lists the RESET configuration options.

Table 6. Reset Configuration

Control Input	Operating Condition	Output
$\overline{\text{RSTN}}$		
0	Device Reset	Hi-Z
0 $\rightarrow$ 1	PLL Recalibration	Hi-Z
1	Normal	Active

7 Output Buffer Termination

This EVM is designed to support proper termination for all three types of output buffers. Proper components must be selected or placed to make sure the chosen output buffer works properly with the correct termination as expected. Figure 4 shows different ways to terminate the outputs of the device.




Figure 4. EVM Output Termination Options

7.1 Output Buffer Examples

LVPECL Output Buffer: Jumpers **J24** and **J26** should be used. This connection is illustrated in Figure 5.




Figure 5. LVPECL Output Setup

LVDS Output Buffer: Remove jumpers **J24** and **J26**. A 100-Ω resistor can be placed at the **R85** placeholder, if necessary. If the output pair is connected to an oscilloscope through 50-Ω SMA cables, then the oscilloscope 50-Ω to ground connection should take care of this termination, and the 100-Ω resistor is no longer necessary. [Figure 6](#) illustrates this output buffer configuration.





Figure 6. LVDS Output Setup

LVC MOS Output Buffer: This LVC MOS buffer typically has 30 Ω internal impedance. An external 22-Ω series resistor is recommended for a 50-Ω impedance characteristic line. For an SMA connection to an oscilloscope, the output can be connected as ac-coupled (using **C52** and **C58**). A lower-than-expected swing will be observed because the LVC MOS driver is **not** capable of driving a 50 Ω to ground load. [Figure 5](#) describes this connection interface.

7.2 Availability of Optional Output

An optional bypassed output (**OSC_OUT**) is only available if the PLL output(s) are chosen at an LVPECL signaling level. **J219** is the SMA placeholder for this output.

8 Schematic



EVALUATION BOARD/KIT IMPORTANT NOTICE

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. **THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.**

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive**.

TI assumes **no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein**.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit www.ti.com/esh.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

EVM WARNINGS AND RESTRICTIONS

It is important to operate this EVM within the input voltage range of 3 V to 3.6 V and the output voltage range of 0 V to 3.6 V.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than +120°C. The EVM is designed to operate properly with certain components above +85°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009-2011, Texas Instruments Incorporated

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated