

LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
			A1	ADD NEW TYPE AND MODIFY MISTAKE	ECO-08-029446	14-NOV-08	Z,Z	BH,Y
		A2	DIMENSION CHANGE	ECO-10-004896	21-FEB-10	Z,Z	BH,Y	
		A3	ADD NEW TYPE	ECO-10-009515	15-MAY-10	Z,Z	BH,Y	

D

C

B



A

D


C

B




A




4.DRILLING DIAGRAM(BOTTOM VIEW)



3.CONNECTION DIAGRAM(BOTTOM VIEW)



NOTE:LOT NO. SYSTEM AS FOLLOWING:





DIMENTION TOLERANCE	
Max. 1mm	±0.1
1mm~Max. 3mm	±0.2
Min. 3mm	±0.3


THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL	FINISH
-	-

DWN	H.SASAKI	Tyco Electronics Corporation ShenZhen, China	
CHK	N.FUNAYAMA		
APVD	A.NAGAI	NAME T7C*5(1)D-**,009 CUSTOMER DRAWING	
PRODUCT SPEC	-		
APPLICATION SPEC	-	SIZE A3	
WEIGHT	-		
CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO 1393190
		RESTRICTED TO	-
		SCALE	4:1
		SHEET	1 OF 3
		REV	A3




THIS DRAWING IS UNPUBLISHED.
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



4.DRILLING DIAGRAM(BOTTOM VIEW)



CONNECTION DIAGRAM(BOTTOM VIEW)



VIEW C


THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	H.SASAKI	Tyco Electronics Corporation ShenZhen, China	
		CHK	N.FUNAYAMA		
DIMENSIONS: mm		APVD	A.NAGAI	NAME T7C*5(1)D-**,009 CUSTOMER DRAWING	
		PRODUCT SPEC	—		
		APPLICATION SPEC	—	SIZE A3 CAGE CODE 00779 DRAWING NO 1393190 RESTRICTED TO —	
		WEIGHT	—		
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE 4:1	SHEET 2 OF 3
				REV	A3

LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

Ⓐ3	FIGURE 11	4-1393190-2	18V	T7CV1D-18	U
Ⓐ1	FIGURE 11	4-1393190-3	24V	T7CV1D-24	t
Ⓐ1	FIGURE 11	4-1393190-1	12V	T7CV1D-12	s
	FIGURE 11	1-1393190-2	24V	T7CS1D-24	r
	FIGURE 11	1-1393190-0	12V	T7CS1D-12	q
	FIGURE 1	6-1393190-3	48V	T7CV5D-48	p
	FIGURE 1	6-1393190-0	24V	T7CV5D-24	o
	FIGURE 1	5-1393190-6	18V	T7CV5D-18	n
	FIGURE 1	5-1393190-3	12V	T7CV5D-12	m
	FIGURE 1	4-1393190-9	9V	T7CV5D-09	l
	FIGURE 1	4-1393190-7	6V	T7CV5D-06	k
	FIGURE 1	4-1393190-6	5V	T7CV5D-05	j
	FIGURE 1	4-1393190-5	3V	T7CV5D-03	i
	FIGURE 1	3-1393190-1	48V	T7CS5D-48	h
	FIGURE 1	2-1393190-8	24V	T7CS5D-24	g
	FIGURE 1	2-1393190-5	18V	T7CS5D-18	f
	FIGURE 1	2-1393190-2	12V	T7CS5D-12	e
	FIGURE 1	2-1393190-0	9V	T7CS5D-09	d
	FIGURE 1	1-1393190-9	6V	T7CS5D-06	c
	FIGURE 1	1-1393190-8	5V	T7CS5D-05	b
	FIGURE 1	1-1393190-7	3V	T7CS5D-03	a
	FIGURE	TE PART NO	PART B	PART A	ITEM

RELAY TYPE

	UV RESIN	UV SEAL(FOR SEALED TYPE)	14
	EPOXY RESIN	SEAL	13
	MW79	MAGNETIC WIRE	12
UL94 V-0	PBT	CASE	11
UL94 V-0 CLASS-F	PET	BOBBIN	10
	CP WIRE	COIL TERMINAL	9
	Ag ALLOY	STATIONARY CONTACT	8
	Ag ALLOY	MOVABLE CONTACT	7
	Cu ALLOY	NC TERMINAL	6
	Cu ALLOY	NO TERMINAL	5
	Cu ALLOY	MOVABLE SPRING	4
	STEEL	CORE	3
	STEEL	ARMATURE	2
	STEEL	YOKE	1
INCOMBUSTIBILITY	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	H.SASAKI		 Tyco Electronics Tyco Electronics Corporation ShenZhen, China		
		CHK	N.FUNAYAMA				
DIMENSIONS: mm		APVD	A.NAGAI			NAME T7C*5(1)D-**,009 CUSTOMER DRAWING	
		PRODUCT SPEC	—				
MATERIAL —	FINISH —	APPLICATION SPEC	—		SIZE A3		
		WEIGHT	—				
		CUSTOMER DRAWING			CAGE CODE 00779	DRAWING NO C= 1393190	RESTRICTED TO —
		SCALE 4:1			SHEET 3 OF 3	REV A3	