





- 1 HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA AND LAST 5.08 [.200] OF THE TAILS.
- 4 ACTION PIN POSTS REQUIRE 1.57[.062] MINIMUM THICK PC BOARD. RECOMMENDED PC BOARD DRILLED HOLES ARE $\phi 1.15 \pm 0.025$ [.0453 ± 0.010] WITH 0.02-0.08 [.001-.003] COPPER AND 0.008 [.0003] MINIMUM TIN-LEAD PLATING. FINISHED HOLE AFTER PLATING IS $\phi 1.02 \pm 0.08$ [.040 ± 0.002].
- 5 TAIL LENGTH AFTER SEATED IN PC BOARD.
- 6 CONTACT POINTS AFTER SEATED IN PC BOARD.
- 7 HOT-STAMPING ON THIS SIDE.
- 8 PART NUMBER AND DATE CODE HOT-STAMPED IN THIS APPROXIMATE AREA.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13[.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

1/2

DWN L. BRINER 1/6/98
CHK R. PATTERSON 1/6/98
APP R. PATTERSON 1/6/98

PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

SIZE
CAGE CODE
DRAWING NO
RESTRICTED TO

tyco
Electronics

Tyco Electronics Corporation
Harriburg, PA 17105-3608

RCPT ASSY, ENHANCED EUROCARD,
VME 64, 160 POSITION

100779
148445

CUSTOMER DRAWING

SCALE 4:1
SHEET 1 OF 1
REV C

1-148445-5
PART NUMBER