



TYPE A - 4 TO 26 WAYS INCLUSIVE:



TYPE B - 2, 3 AND 27 TO 36 WAYS:



GENERAL:

- NOTES:
1. 2 & 3 WAY: LENGTH = $2.54 \times \text{No. OF PITCHES} + 2.48 \text{ MAX}$ (MOULDED).
 - 27 TO 36 WAYS: LENGTH = $2.54 \times \text{No. OF PITCHES} + 3.30 \text{ MAX}$ (MACHINED).
 2. RECOMMENDED PCB HOLE = $\pm 0.85 \text{ MIN.}$
 3. MAXIMUM PIN LENGTH = 7.0mm.
 4. MATERIAL:
MOULDING = GLASS-FILLED POLYESTER UL94V-0, BLACK.
CONTACTS = PHOSPHOR BRONZE.
 5. FINISH:
06 = 90/10 TINLEAD.
22 = GOLD ON CONTACT FACE OVER NICKEL,
90/10 TINLEAD ON TAILS.

ORDER CODE:	
M20-982XXXX	
No. OF WAYS	
02 TO 36	
FINISH	
06 = TINLEAD	
22 = SELECTIVE GOLD	

CUSTOMER
INFORMATION
SHEET

14	05.08.95	3476
13	11.05.95	3352
12	17.11.95	3104
11	25.03.95	3049
3	10.02.94	2536
2	17.03.93	2223
1	13.09.93	----

ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN: W. BOURNE		
CUSTOMER REF.		
ASSEMBLY DRO:		

HARWIN

HARWIN INC
U.S.A.

TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.

TEL: 01705 370451
FAX: 01705 324010

HARWIN PTE
SINGAPORE

TEL: 65 7794903
FAX: 65 7793868

HARWIN CONNECTORS
KOREA

TEL: 822 521 0747
FAX: 822 521 0749

TOLERANCE:

X. = $\pm 1 \text{ mm}$
X.X = $\pm 0.25 \text{ mm}$
X.XXX = $\pm 0.10 \text{ mm}$
X.XXX = $\pm 0.075 \text{ mm}$

ANGLES = $\pm 1^\circ$
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE TABLE

AREA: mm²

TITLE:

2.54mm SIL VER
SOCKET (NARR)

DRAWING NUMBER:

M20-982XXXX

SH1
2
OF
2