

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

.19




© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER 0G3A-0451-00	24JUL00	MF	KR



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS 0.36-0.57mm [#27-#23] AWG COPPER MAGNET WIRE. A SINGLE WIRE ONLY.
- 3 POKE-IN ACCEPTS A 0.50-0.90mm² [#20-#18] AWG SOLID OR FUSED STRANDED LEAD WIRE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26JUL1999 MICHAEL S. FEHER		WITHOUT PAPER		1217182-1	
		CHK 26JUL1999 PETE DESANTIS		REELING		PART NUMBER	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 26JUL1999 KURT A. RANDOLPH		NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [.010] 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC		AMP Incorporated	
				108-2012		Harrisburg, PA 17105-3608	
MATERIAL		FINISH		APPLICATION SPEC		SIZE	
4M BRASS		0.002032 [.000080]		114-2046		CAGE CODE	
		MIN TIN PLATE		WEIGHT		DRAWING NO	
				CUSTOMER DRAWING		A2 00779 C- 1217182	
						RESTRICTED TO	
						SCALE	
						10:1	
						SHEET	
						1 OF 1	
						REV	
						B	