


- NOTES:
- 1.0 MATERIALS:
 - 1.1 HOUSING & NUTS: STAINLESS STEEL PER ASTM-A582, TYPE 303.
 - 1.2 CENTER CONTACT: BERYLLIUM COPPER ROD ALLOY C172, PER ASTM-B196.
 - 1.3 DIELECTRIC: PTFE FLUOROCARBON PER ASTM-D1457.
 - 2.0 PLATING:
 - 2.1 HOUSING & NUTS: PASSIVATED PER MIL-F-14072 AND QQ-P-35
 - 2.2 CENTER CONTACT: GOLD PER MIL-G-45204, TYPE II, CLASS 2.
 - 3.0 ELECTRICAL SPECIFICATIONS:
 - 3.1 FREQUENCY RANGE: DC to 26.5 GHz
 - 3.2 VSWR (MAX.):
 - DC to 20 GHz: 1.10:1
 - 20 to 26.5 GHz: 1.15:1
 - 4.0 MARKING: MARK UNIT AS SHOWN
 - 5.0 DIMENSIONS IN PARENTHESIS ARE IN MILLIMETERS.



MODEL NUMBER
ADT-2734-MM-3MM-02

DWG NO. WAS: 05516-01-00

REV.	DESCRIPTION	DATE
-	RELEASED	8/29/84
A	ECR 3701	7/2/85
B	ECR 6545	7/31/89
C	REDRAW ON CAD	11/20/92
D	ECO 23382	3/14/11

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.		CAGE CODE 34078		MIDWEST MICROWAVE	
		 EMERSON Network Power Connectivity Solutions		TITLE ADAPTER – 3.5MM PLUG TO 3.5MM PLUG OUTLINE DRAWING	
UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°		DRAWN/DATE A.BEATTY 11/20/92	ENG./DATE A.OSGA 11/20/92	DRAWING NUMBER ADT-2734-MM-3MM-02-01	
		CHECKED/DATE M.HOLLMAN 11/20/92	APPROVED/DATE	SCALE: 5=1	REV. D
		SHEET 1 of 1			