

CONTACTOR RELAY, LATCHED, 4-POLE,
4 NO, SIZE S00, DC 110 V

**General details:**

product brand name	SIRIUS	
product designation	contactor relay	
Size of the contactor	S00	
Protection class IP / on the front	IP20	
Degree of pollution	3	
Insulation voltage / with degree of pollution 3 / rated value	V	690
Installation altitude / at a height over sea level / maximum	m	2,000
Ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operating	°C	-25 ... +60
Contact reliability	one incorrect switching operation of 100 million switching operations (17 V, 1 mA)	
Resistance against shock	10g / 5 ms and 5g / 10 ms	
Impulse voltage resistance / rated value	kV	6
Item designation		
• according to DIN EN 61346-2		K
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		K
Mechanical operating cycles as operating time		

• of the contactor / typical		30,000,000
• of the contactor with added auxiliary switch block / typical		10,000,000
• of the contactor with added electronics-compatible auxiliary switch block / typical		5,000,000

Control circuit:

Type of voltage / of the controlled supply voltage		DC
Control supply voltage / 1		
• for DC / rated value	V	110
Working range factor supply voltage rated value / of the magnet coil		
• for DC		0.8 ... 1.1
Pull-in power / of the solenoid / for DC	W	3.2
Holding power / of the solenoid / for DC	W	3.2

Auxiliary circuit:

Product extension / auxiliary switch		Yes
Identification number and letter for switching elements		40 E
Contact reliability / of the auxiliary contacts		1 faulty switching per 100 million (17 V, 1 mA)
Number of NC contacts / for auxiliary contacts		0
• delayed switching		0
• instantaneous switching		0
• asynchronous switching		0
• lagging switching		0
Number of NO contacts / for auxiliary contacts		4
• instantaneous switching		4
• delayed switching		0
• asynchronous switching		0
• leading switching		0
Number of changeover contacts		
• for auxiliary contacts		0
• of the auxiliary contacts / instantaneous switching		0
Operating current / of the auxiliary contacts		
• at AC-12 / maximum	A	10
• at AC-15		
• at 230 V	A	6
• at 400 V	A	3
• at 500 V	A	2
• at 690 V	A	1
• with 1 current path		
• at DC-12		

• at 24 V	A	10
• at 110 V	A	3
• at 220 V	A	1
• at DC-13		
• at 24 V	A	10
• at 110 V	A	1
• at 220 V	A	0.27

Short-circuit:

Design of the fuse link / for short-circuit protection of the auxiliary switch / required		fuse gL/gG: 10 A
--	--	------------------

Installation/mounting/dimensions:

Built in orientation		with vertical mounting surface +/-180° rotatable, with vertical mounting surface +/- 30° tiltable to the front and back
Type of mounting		screw and snap-on mounting
Width	mm	90
Height	mm	57.5
Depth	mm	72
Distance, to be maintained, to the ranks assembly / sideways	mm	0

Connections:

Design of the electrical connection / for auxiliary and control current circuit		screw-type terminals
Type of the connectable conductor cross-section		
• for auxiliary contacts		
• solid		2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²), 2x 4 mm ²
• finely stranded		2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
• with conductor end processing		2x (20 ... 16), 2x (18 ... 14), 1x 12
• for AWG conductors / for auxiliary contacts		

Certificates/approvals:

Verification of suitability		CSA / UL / CCC / GL / LRS / BV / DNV / RMRS / RINA
------------------------------------	--	--

General Product Approval	Functional Safety / Safety of Machinery	Test Certificates
--------------------------	---	-------------------



[ROSTEST](#)



[SUVA](#)

[Manufacturer](#)

Shipping Approval

other



[Manufacturer](#)

Safety:

Proportion of dangerous failures

• with high demand rate / according to SN 31920	%	75
• with low demand rate / according to SN 31920	%	40

T1 value / for proof test interval or service life / according to IEC 61508

a 20

Protection against electrical shock

finger-safe

B10 value / with high demand rate / according to SN 31920

1,000,000

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAx-Online-Generator


<http://www.siemens.com/cax>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RH1440-1BF40/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RH1440-1BF40





last change:

Feb 6, 2012