



MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



- NOTES:
1. TERMINATION: TIN PLATED OVER FIRED ON SILVER, WITH A NICKEL BARRIER.
 2. THIS END LAPPED.

TUSONIX STYLE	6003
RESONATOR TYPE	QUARTER WAVE
RESONANCE FREQUENCY	2300 MHz $\pm 1\%$
K	20 (NOM)
TEMP. COEFFICIENT	± 10 PPM/ $^{\circ}$ C
QUALITY FACTOR Q	> 300

X-2015 Rev-0	REVISION RECORD			--TOLERANCES-- Unless Otherwise Specified		Title 2300 MHz COAXIAL RESONATOR		
	Original Release C.O.		DECIMAL ±	.010 [0.25]				
	WAS SK 8207-6003-014- 2300-E0C1. S.M. 12-13-06		0	CORRECTED P/N WAS EOC1. S.M. 12-13-06-07		Drawn	S.M. 09-28-06	Scale 6 X
	20061003-1-06				TUSONIX TUCSON, ARIZONA	Approved M.M. 09-28-06		
	20070208-3-07		1			A	6003-014-2300-E0C1	
	ADDED NOTE 2 & REVISED NOTE 1. S.M. 10-08-07		2					
20071017-1-03								