

NOTES:

① **MAT'L:** COPPER (STOCK TKN. $\frac{.040}{.02}$ $\pm .001$)


PLATING: ELECTRO TIN (.0003 MIN)

TIN-PLATED BRASS FUNNEL FERRULE

③ NYLON INSULATION (COLOR CODED)

YELLOW)
STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
16 = .328
38 = .390



"UL" LISTING # E32244
"CSA" LISTING # 18689

WIRE SIZE: 12 - 10 AWG
4.0 - 6.0 MM²

ALL DIMENSIONS = INCHES (MWID) = DENOTES MAXIMUM WIRE INSULATION DIAMETER

PART NUMBER	"W" $\pm .010$	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES
C-5102	<u>.415</u> 10.41	<u>.305</u> 7.75	<u>.1204</u> 30.58	08
C-5105-	<u>.320</u> 8.13	<u>.305</u> 7.75	<u>.1204</u> 30.58	06

FILE NO. C-CD-503 - 01

DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE:	NTS	DATE	TITLE:	
FRAC.	DEC.	REV. 10/20/93 RUM 1/6/94	DRWN. BY:	JJ	11-15-84	SPADE TONGUE	ETC molex
			CHKD. BY:	GZ	11-26-84	TERMINAL	INCORPORATED
±	±		APPRO. BY:			AVIKRIMP	500-SERIES

DWG. NO. A CUSTOMER DWG.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[19137-0038](#)