


External Dimensions



Frame: Aluminum Alloy
 Impeller: Plastic (UL:94V-0)
 Bearing: Ball bearing
 Lead wire: UL1430AWG22
 OPERATING TEMP*: -10C~70C
 *: -10C~60C for fans with sleeve/ball combination bearings.

Specifications(Nominal)


*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ○=1B1S ●=Hypro bearing


Frame size (mm)	Model No.	Bearing System Type	Volt./Freq. (VAC/Hz)	Rated Current (A)	Rated Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	*Noise Level (dB/A)	Weight (g)	
172x150x51	AK1751HB	◎	100-115/50	0.24	26.00	2700	5.100	180.00	0.533	13.53	63.0±2	1050	
			100-115/60	0.25	28.60	3100	5.950	210.00	0.697	17.70	63.0±2		
	AK1751MB	◎	100-115/50	0.15	17.25	2450	4.700	165.00	0.422	10.71	56.8±2		
			100-115/60	0.18	21.16	2580	4.800	170.00	0.412	10.46	58.3±2		
	AK1752HB	◎	◎	200-240/50	0.13	26.68	2700	5.100	180.00	0.558	14.17		50.0±2
				200-240/60	0.15	31.97	3100	5.950	210.00	0.700	17.78		56.7±2
AK1752MB	◎	◎	200-240/50	0.10	20.00	2500	4.285	151.40	0.410	10.41	56.6±2		
			200-240/60	0.10	23.00	2500	4.245	150.00	0.360	9.14	56.5±2		

Specifications subject to change without notice.

AK1751HB



AK1751MB



*Safety approvals

				
✓	✓		✓	✓